

SAFETY DATA SHEET

Issuing Date No data available

Revision Date 02-Feb-2015

Revision Number 1

The supplier identified below generated this SDS using the UL SDS template. UL did not test, certify, or approve the substance described in this SDS, and all information in this SDS was provided by the supplier or was reproduced from publically available regulatory data sources. UL makes no representations or warranties regarding the completeness or accuracy of the information in this SDS and disclaims all liability in connection with the use of this information or the substance described in this SDS. The layout, appearance and format of this SDS is © 2014 UL LLC. All rights reserved.

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product identifier

Product Name Earth Enzymes (9704)

Other means of identification

Synonyms None

Recommended use of the chemical and restrictions on use

Recommended Use Drain openers

Uses advised against No information available

Details of the supplier of the safety data sheet

Supplier Name VENUS LABORATORIES dba Earth Friendly Products

Supplier Address
111 S ROHLWING ROAD
ADDISON IL
60101
US

Supplier Phone Number Phone:800-592-1900

Emergency telephone number Chemtrec: 800-424-9300

2. HAZARDS IDENTIFICATION

Classification

This chemical is not considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

GHS Label elements, including precautionary statements

Emergency Overview

The product contains no substances which at their given concentration, are considered to be hazardous to health

Appearance White

Physical State Granular Solid

Odor None

Precautionary Statements - Prevention

Obtain special instructions before use

Precautionary Statements - Response

None

Precautionary Statements - Storage

None

Precautionary Statements - Disposal

None

Hazards not otherwise classified (HNOC)

Not applicable

Unknown Toxicity

100% of the mixture consists of ingredient(s) of unknown toxicity

Other information

May cause slight eye irritation

Interactions with Other Chemicals

No information available.

3. COMPOSITION/INFORMATION ON INGREDIENTS

The product contains no substances which at their given concentration, are considered to be hazardous to health.

4. FIRST AID MEASURES

First aid measures**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Keep eye wide open while rinsing. Remove contact lenses, if present and if irritation persists consult a doctor/physician.

Skin Contact

Wash off immediately with soap and plenty of water for at least 15 minutes. May cause an allergic skin reaction. In the case of skin irritation or allergic reactions see a physician.

Inhalation

Remove to fresh air. If symptoms persist, call a physician.

Ingestion

Do NOT induce vomiting. Drink plenty of water. If symptoms persist, call a physician.

Most important symptoms and effects, both acute and delayed**Most Important Symptoms and Effects**

No information available.

Indication of any immediate medical attention and special treatment needed**Notes to Physician**

Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

CAUTION: Use of water spray when fighting fire may be inefficient.

Specific Hazards Arising from the Chemical

No information available.

Uniform Fire Code

Irritant: Solid

Hazardous Combustion Products

Carbon oxides.

Explosion Data

Sensitivity to Mechanical Impact No.

Sensitivity to Static Discharge No.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal Precautions

Avoid contact with eyes.

Environmental Precautions

Environmental Precautions

Refer to protective measures listed in Sections 7 and 8.

Methods and material for containment and cleaning up

Methods for Containment

Prevent further leakage or spillage if safe to do so.

Methods for cleaning up

Pick up and transfer to properly labeled containers. Use personal protective equipment as required. Cover powder spill with plastic sheet or tarp to minimize spreading and keep powder dry. Avoid generation of dust. Clean contaminated surface thoroughly.

7. HANDLING AND STORAGE

Precautions for safe handling

Handling

Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Do not eat, drink or smoke when using this product.

Conditions for safe storage, including any incompatibilities

Storage

Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible Products

None known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies

Appropriate engineering controls

Engineering Measures

Showers
Eyewash
stations
Ventilation systems

Individual protection measures, such as personal protective equipment

Eye/Face Protection

No special protective equipment required.

Skin and Body Protection

No special protective equipment required.

Respiratory Protection

No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

Hygiene Measures

Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical and Chemical Properties		
Physical State	Granular, Solid	
Appearance Color	White No information available	Odor Odor Threshold None No information available
Property pH Melting / freezing point Boiling point / boiling range Flash Point Evaporation Rate Flammability (solid, gas)	Values No data available No data available No data available No data available No data available No data available	Remarks_Method None known None known None known None known None known None known
Flammability Limit in Air		
Upper flammability limit	No data available	
Lower flammability limit	No data available	No data available
Vapor pressure	No data available	None known
Vapor density	No data available	None known
Specific Gravity	No data available	None known
Water Solubility	Soluble	None known
Solubility in other solvents	No data available	None known
Partition coefficient: n-octanol/water	No data available	None known
Autoignition temperature	No data available	None known
Decomposition temperature	No data available	None known
Kinematic viscosity	No data available	None known
Dynamic viscosity	No data available	None known
Explosive properties	No data available	None known
Oxidizing Properties	No data available	None known
Other Information		
Softening Point	No data available	No data available
VOC Content (%)	No data available	No data available
Particle Size	No data available	No data available
Particle Size Distribution		

10. STABILITY AND REACTIVITY

Reactivity

No data available.

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Hazardous Polymerization

Hazardous polymerization does not occur.

Conditions to avoid

None known.

Incompatible materials

None known.

Hazardous Decomposition Products

Carbon oxides.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Product does not present an acute toxicity hazard based on known or supplied information.

Inhalation

Specific test data for the substance or mixture is not available.

Eye Contact

Specific test data for the substance or mixture is not available.

Skin Contact

Specific test data for the substance or mixture is not available.

Ingestion

Specific test data for the substance or mixture is not available.

Component Information

Information on toxicological effects

Symptoms

No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization

No information available.

Mutagenic Effects

No information available.

Carcinogenicity

Contains no ingredient listed as a carcinogen.

Reproductive Toxicity

No information available.

STOT - single exposure

No information available.

STOT - repeated exposure

No information available.

Chronic Toxicity No known effect based on information supplied.

Target Organ Effects None known.

Aspiration Hazard No information available.

Numerical measures of toxicity. Product Information

The following values are calculated based on chapter 3.1 of the GHS document

Not applicable

12. ECOLOGICAL INFORMATION

Ecotoxicity

The environmental impact of this product has not been fully investigated.

Persistence and Degradability

No information available.

Bioaccumulation

No information available

Other adverse effects

No information available.

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal methods

This material, as supplied, is not a hazardous waste according to Federal regulations (40 CFR 261). This material could become a hazardous waste if it is mixed with or otherwise comes in contact with a hazardous waste, if chemical additions are made to this material, or if the material is processed or otherwise altered. Consult 40 CFR 261 to determine whether the altered material is a hazardous waste. Consult the appropriate state, regional, or local regulations for additional requirements.

Contaminated Packaging Dispose of contents/containers in accordance with local regulations.

California Hazardous Waste Codes

141

14. TRANSPORT INFORMATION

DOT

**Proper Shipping Name
Hazard Class**

NOT REGULATED
NON REGULATED
N/A

TDG

Not regulated

MEX

Not regulated

ICAO

Not regulated

IATA

**Proper Shipping Name
Hazard Class**

Not regulated
NON REGULATED
N/A

IMDG/IMO	Not regulated
Hazard Class	N/A

RID	Not regulated
------------	---------------

ADR	Not regulated
------------	---------------

ADN	Not regulated
------------	---------------

International Inventories

15. REGULATORY INFORMATION

TSCA	Complies
DSL	All components are listed either on the DSL or NDSL.

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute Health Hazard	No
Chronic Health Hazard	No
Fire Hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

This product does not contain any substances regulated by state right-to-know regulations.

International Regulations

Canada

WHMIS Hazard Class

D2B - Toxic materials

16. OTHER INFORMATION

NFPA	Health Hazards 1	Flammability 0	Instability 0	Physical and Chemical Hazards -
HMIS	Health Hazards 1	Flammability 0		
Physical Hazard 0	Personal Protection			
		X		

Prepared By	Product Stewardship 23 British American Blvd. Latham, NY 12110 1-800-572-6501
Revision Date	02-Feb-2015
Revision Note	No information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet