

# ALB753B



32" x 23.63" x 23.5" (H x W x D)

ADA compliant built-in undercounter all-refrigerator for general purpose use, auto defrost w/SS door frame for panel inserts and black cabinet

### Highlights:

32" height for use under lower ADA compliant counters

Flexible design allows built-in or freestanding use in 24" spaces

Stainless steel door frame accepts slide-in panels for a custom look

Automatic defrost ensures minimum user maintenance

### Product Features:

ADA Compliant	32 inch height is designed to fit under ADA compliant counters
Slim undercounter dimensions	Less than 24 inches wide, with a generous 5.5 c.f. of storage capacity
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinetry
Fully finished black cabinet	Allows the unit to be used freestanding
Stainless steel door frame	Two-piece "U"-shaped door frame accepts slide-in panels for a custom look. Handle included
Automatic defrost	No-frost convenience for reduced user maintenance
Adjustable glass shelves	Rearrange interior space to fit any sized item or remove shelves for simple cleanup
Flat door liner	An easy-to-clean flat liner accepts large trays
Interior light on rocker switch	Turn the light on when you need it and off when you're done with a convenient switch located behind the thermostat

**ALB753B Specifications:**

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Depth with Handle	25.13"
Depth with door at 90°	45.63"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Panel-Ready
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Energy Usage/Year	405.0kWh/year
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	112.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	88.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	26.25"
Interior Width	21.0"
Interior Depth	17.75"
Compressor Step Height	5.5"
Compressor Step Width	21.0"

Compressor Step Depth

