

# SAFETY DATA SHEET

Issuing Date No data available

Revision Date 09-May-2017

Revision Number 2



The supplier identified below generated this SDS using the UL SDS template. UL did not test, certify, or approve the substance described in this SDS, and all information in this SDS was provided by the supplier or was reproduced from publically available regulatory data sources. UL makes no representations or warranties regarding the completeness or accuracy of the information in this SDS and disclaims all liability in connection with the use of this information or the substance described in this SDS. The layout, appearance and format of this SDS is © 2014 UL LLC. All rights reserved.

## 1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

### Product identifier

Product Name ECOS Dishmate Pear (9720)

### Other means of identification

Synonyms None

### Recommended use of the chemical and restrictions on use

Recommended Use Liquid dishwashing soap

Uses advised against No information available

### Details of the supplier of the safety data sheet

Supplier Name Venus Labs/dba Earth Friendly Products  
Supplier Address 111. S Rohlwing Rd Addison, IL 60101  
Supplier Phone Number Phone: 800-451-9304  
Emergency telephone number Chemtrec: 800-424-9300

## 2. HAZARDS IDENTIFICATION

### Classification


This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200).

Serious eye damage/eye irritation

Category 2A

### GHS Label elements, including precautionary statements



Emergency Overview		
<b>Signal word</b>	<b>Warning</b>	
<b>Hazard Statements</b>		
May cause eye irritation		
		
<b>Appearance</b>	Clear	<b>Physical state</b> Viscous liquid
		<b>Odor</b> Pear

**Precautionary Statements - Prevention**

Wash face, hands and any exposed skin thoroughly after handling  
 Wear protective gloves/protective clothing/eye protection/face protection  
 Avoid breathing dust/fume/gas/mist/vapors/spray  
 Remove the contaminated clothing and wash.

**Precautionary Statements - Response**

Specific treatment (see supplemental first aid instructions on this label)

**Eyes**

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
 If irritation persists consult a doctor/physician.

**Skin**

IF ON SKIN: No adverse reaction expected. Wash with soap and water  
 Take off contaminated clothing and wash before reuse  
 If skin irritation or rash occurs: Get medical advice/attention

**Precautionary Statements - Storage**

None

**Precautionary Statements - Disposal**

None

**Hazards not otherwise classified (HNOC)**

Not applicable

**Unknown Toxicity**

12.7% of the mixture consists of ingredient(s) of unknown toxicity

**Other information**

May be harmful if swallowed  
 Harmful to aquatic life with long lasting effects

**Interactions with Other Chemicals**

No information available.

### 3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No	Weight-%	Trade Secret
Sodium coco sulfate	97375-27-4	2.5 - 10	*
Cocamidopropylamine oxide	68155-09-9	0.1 - 2.5	*
Lauramine oxide	1643-20-5	0.1 - 2.5	*

\*The exact percentage (concentration) of composition has been withheld as a trade secret

### 4. FIRST AID MEASURES

#### First aid measures

##### General Advice

Show this safety data sheet to the doctor in attendance.

##### Eye contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Keep eye wide open while rinsing. Remove contact lenses, if present and If irritation persists consult a doctor/physician.

##### Skin contact

Wash off immediately with soap and plenty of water for at least 15 minutes. May cause an allergic skin reaction. In the case of skin irritation or allergic reactions see a physician.

##### Inhalation

Remove to fresh air. Get medical attention immediately if symptoms occur.

##### Ingestion

Rinse mouth immediately and drink plenty of water. Never give anything by mouth to an unconscious person. Do NOT induce vomiting. Call a physician.

##### Self-protection of the first aider

Avoid contact with skin, eyes or clothing. Use personal protective equipment as required. Wear personal protective clothing (see section 8).

#### Most important symptoms and effects, both acute and delayed

##### Most Important Symptoms and Effects

Burning sensation.

#### Indication of any immediate medical attention and special treatment needed

##### Notes to Physician

Treat symptomatically.

## 5. FIRE-FIGHTING MEASURES

### **Suitable Extinguishing Media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

### **Unsuitable extinguishing media**

CAUTION: Use of water spray when fighting fire may be inefficient.

### **Specific hazards arising from the chemical**

No information available.

#### **Uniform Fire Code**

Irritant: Liquid

### **Hazardous Combustion Products**

Carbon oxides.

### **Explosion Data**

**Sensitivity to Mechanical Impact** No.

**Sensitivity to Static Discharge** No.

### **Protective equipment and precautions for firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

## 6. ACCIDENTAL RELEASE MEASURES

### **Personal precautions, protective equipment and emergency procedures**

#### **Personal precautions**

Avoid contact with skin, eyes or clothing. Use personal protective equipment as required.

#### **Other Information**

Refer to protective measures listed in Sections 7 and 8.

### **Environmental precautions**

#### **Environmental precautions**

Prevent further leakage or spillage if safe to do so.

### **Methods and material for containment and cleaning up**

#### **Methods for containment**

Prevent further leakage or spillage if safe to do so.

#### **Methods for cleaning up**

Soak up with inert absorbent material. Pick up and transfer to properly labeled containers.

## 7. HANDLING AND STORAGE

### Precautions for safe handling

**Handling** Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Do not eat, drink or smoke when using this product..

### Conditions for safe storage, including any incompatibilities

**Storage** Keep containers tightly closed in a dry, cool and well-ventilated place. Store locked up. Keep out of the reach of children.

**Incompatible Products** Strong acids. Strong oxidizing agents. Strong bases.

## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control parameters

**Exposure Guidelines** This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies

### Appropriate engineering controls

**Engineering Measures** Showers  
Eyewash stations  
Ventilation systems

### Individual protection measures, such as personal protective equipment

**Eye/face protection** None required for consumer use. If there is a risk of contact.. Tight sealing safety goggles.

**Skin and body protection** None required for consumer use. If there is a risk of contact.. Wear protective gloves and protective clothing. Long sleeved clothing. Impervious gloves.

**Respiratory protection** No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Wear suitable gloves and eye/face protection. Do not eat, drink or smoke when using this product.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

### Physical and Chemical Properties

<b>Physical state</b>	Viscous Liquid	<b>Odor</b>	Pear
<b>Appearance</b>	Clear	<b>Odor Threshold</b>	No information available
<b>Color</b>	No information available		
<b><u>Property</u></b>	<b><u>Values</u></b>	<b><u>Remarks</u></b>	<b><u>Method</u></b>
<b>pH</b>	7.75-8.50	None known	
<b>Melting / freezing point</b>	No data available	None known	
<b>Boiling point / boiling range</b>	212°F	None known	

<b>Flash Point</b>	No data available	None known
<b>Evaporation Rate</b>	No data available	None known
<b>Flammability (solid, gas)</b>	No data available	None known
<b>Flammability Limit in Air</b>		
<b>Upper flammability limit</b>	No data available	
<b>Lower flammability limit</b>	No data available	
<b>Vapor pressure</b>	No data available	None known
<b>Vapor density</b>	No data available	None known
<b>Specific Gravity</b>	1.010	None known
<b>Water Solubility</b>	Miscible in water	None known
<b>Solubility in other solvents</b>	No data available	None known
<b>Partition coefficient: n-octanol/water</b>	No data available	None known
<b>Autoignition temperature</b>	No data available	None known
<b>Decomposition temperature</b>	No data available	None known
<b>Kinematic viscosity</b>	No data available	None known
<b>Dynamic viscosity</b>	No data available	None known
<b>Explosive properties</b>	No data available	
<b>Oxidizing properties</b>	No data available	

**Other Information**

<b>Softening Point</b>	No data available
<b>VOC Content (%)</b>	No data available
<b>Particle Size</b>	No data available
<b>Particle Size Distribution</b>	

## 10. STABILITY AND REACTIVITY

**Reactivity**

No data available.

**Chemical stability**

Stable under recommended storage conditions.

**Possibility of Hazardous Reactions**

None under normal processing.

**Hazardous Polymerization**

Hazardous polymerization does not occur.

**Conditions to avoid**

None known based on information supplied.

**Incompatible materials**

Strong acids. Strong oxidizing agents. Strong bases.

**Hazardous Decomposition Products**

Carbon oxides.

## 11. TOXICOLOGICAL INFORMATION

**Information on likely routes of exposure****Product Information****Inhalation**

Specific test data for the substance or mixture is not available. No irritation expected.

**Eye contact**

Specific test data for the substance or mixture is not available. Not expected to be an irritant based on components. May Cause Eye Irritation. May cause burns.



**Skin contact** Specific test data for the substance or mixture is not available. Not expected to be a skin irritant based on components. Prolonged contact may cause redness and irritation.

**Ingestion** Specific test data for the substance or mixture is not available. Ingestion may cause irritation to mucous membranes. Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea.

### Component Information

#### Information on toxicological effects

**Symptoms** Erythema (skin redness). May cause redness and tearing of the eyes. Itching. Rashes. Hives.

#### Delayed and immediate effects as well as chronic effects from short and long-term exposure

**Sensitization** No information available.

**Mutagenic Effects** No information available.

**Carcinogenicity** Contains no ingredient listed as a carcinogen.

**Reproductive toxicity** No information available.

**STOT - single exposure** No information available.

**STOT - repeated exposure** No information available.

**Chronic Toxicity** No known effect based on information supplied.

**Target Organ Effects** Respiratory system. Eyes. Skin.

**Aspiration Hazard** No information available.

#### Numerical measures of toxicity Product Information

The following values are calculated based on chapter 3.1 of the GHS document

**ATEmix (oral)**  
4,595.00 mg/kg

## 12. ECOLOGICAL INFORMATION

### Ecotoxicity

Toxic to aquatic organisms. Harmful to aquatic life with long lasting effects.

### Persistence and Degradability

No information available.

### Bioaccumulation

No information available

### Other adverse effects

No information available.

## 13. DISPOSAL CONSIDERATIONS

### Waste treatment methods

#### **Disposal methods**

This material, as supplied, is not a hazardous waste according to Federal regulations (40 CFR 261). This material could become a hazardous waste if it is mixed with or otherwise comes in contact with a hazardous waste, if chemical additions are made to this material, or if the material is processed or otherwise altered. Consult 40 CFR 261 to determine whether the altered material is a hazardous waste. Consult the appropriate state, regional, or local regulations for additional requirements.

#### **Contaminated Packaging**

Dispose of contents/containers in accordance with local regulations.

California Hazardous Waste Codes 561

## 14. TRANSPORT INFORMATION

<b><u>DOT</u></b>	NOT REGULATED
Proper Shipping Name	NON REGULATED
Hazard Class	N/A
<b><u>IDG</u></b>	Not regulated
<b><u>MEX</u></b>	Not regulated
<b><u>ICAO</u></b>	Not regulated
<b><u>IATA</u></b>	Not regulated
Proper Shipping Name	NON REGULATED
Hazard Class	N/A
<b><u>IMDG/IMO</u></b>	Not regulated
Hazard Class	N/A
<b><u>RID</u></b>	Not regulated
<b><u>ADR</u></b>	Not regulated





**ADN** Not regulated

**15. REGULATORY INFORMATION**

**International Inventories**

TSCA Complies  
 DSL All components are listed either on the DSL or NDSL.

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory  
 DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

**US Federal Regulations**

**SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

**SARA 311/312 Hazard Categories**

Acute Health Hazard	Yes
Chronic Health Hazard	No
Fire Hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

**CWA (Clean Water Act)**

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

**CERCLA**

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

**US State Regulations**

**California Proposition 65**

This product does not contain any Proposition 65 chemicals.

**U.S. State Right-to-Know Regulations**

This product does not contain any substances regulated by state right-to-know regulations.

**International Regulations**

**Canada**

**WHMIS Hazard Class**

Not determined

**16. OTHER INFORMATION**

NFPA	Health Hazards 1	Flammability 0	Instability 0	Physical and Chemical Hazards - Personal Protection X
HMIS	Health Hazards 1	Flammability 0	Physical Hazard 0	



**Revision Date** 09-May-2017  
**Revision Note** No information available

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**