

ALB753LBL



32" x 23.63" x 23.5" (H x W x D)

ADA compliant built-in undercounter all-refrigerator for general purpose use, auto defrost w/SS door frame for panel inserts, lock, and black cabinet

Highlights:

32" height for use under lower ADA compliant counters

Flexible design allows built-in or freestanding use in 24" spaces

Factory installed front lock offers convenient security for stored items

Stainless steel door frame accepts slide-in panels for a custom look

Product Features:

ADA compliant	32 inch height fits under standard ADA counters
Slim undercounter dimensions	Less than 24 inches wide with a full 5.5 c.f. capacity
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Fully finished black cabinet	Allows the unit to be used freestanding
Factory installed lock	Keyed lock offers added security
Stainless steel door frame	Two-piece "U"-shaped door frame accepts slide-in panels for a custom look. Handle included
Reversible door	User-reversible door swing for added flexibility
Automatic defrost	No-frost convenience for reduced user maintenance
One piece interior liner	Easy clean-up with a seamless liner that won't hold a mess in hidden crevices

ALB753LBL Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Depth with Handle	24.63"
Depth with door at 90°	45.13"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Panel-Ready
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Energy Usage/Year	405.0kWh/year
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	105.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	2
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"
Interior Depth	17.5"
Compressor Step Height	7.0"
Compressor Step Width	20.0"

Compressor Step Depth

