



Stainless design.  
Stellar performance.  
Superior value.

AUC27R  
Refrigerator

AUC27F  
Freezer

## Single Door Under-Counter/ Worktop Refrigerators and Freezers

- *Tested to NSF Standard 7 requirements for open food storage.*
- *All Arctic Air products come with full one year parts and labor warranties and a five year compressor warranty.*




*Arctic Air products must pass numerous quality control inspections throughout the manufacturing process.*

*All products are operated and monitored for a minimum of thirteen hours prior to packaging and shipping.*

# Single Door Under-Counter Worktop Refrigerators and Freezers


Stainless design. Stellar performance. Superior value.

- 
- All units come standard with heavy-duty worktop surface.
  - Standard top panel is removable for use in lower height applications (reduces total height by 1.5").
  - Exterior cabinet construction consists of full stainless steel front and sides.
  - One adjustable, heavy-duty epoxy coated wire shelves.
  - Interior cabinet is bright white ABS liner with full stainless steel floor white coved corners.
  - Condensate heating element built into condensate pan for efficient evaporation of excess water.
  - Electronic thermostat with external digital LED display for accurate control and easy reading
  - Easy to mount casters (two lockable) are standard with all units.
  - Self closing doors that remain open at 90 degrees.
  - Solid door construction with foamed-in-place recessed handle.
  - Freezer door frames have integral factory installed heating element to eliminate condensation.
  - Magnetic door gaskets are removable and replaceable without tools.
  - Larger fan motors and blades for more efficient air flow ensuring faster recovery times.
  - Self contained capillary tube system using environmentally friendly CFC free refrigerant (R404A in freezers and R134A in refrigerators).
  - Tested to NSF Standard 7 requirements for open food storage.
  - All Arctic Air products come with full one year parts and labor warranties and a five year compressor warranty.

Model Number	External Dimensions			Doors	Shelves	Cubic Feet	Temperature Range	Cord Length	HP	Amps	NEMA Plug	Crated Weight (lbs.)
	Width	Depth*	Height**									
<b>AUC27R</b>	27.875"	30.0"	35.625"	1	1	6.5	33°F to 41°F	8'	3/8	5	5-15P	185
<b>AUC27F</b>	27.875"	30.0"	35.625"	1	1	6.5	-10°F to +10°F	8'	1/2	7	5-15P	190

\*Depth with door open 90° — AUC27R/AUC427F = 54.75"  
 \*\*Height includes 3" for casters. Height with worktop panel removed = 34.125"

**Optional Shelf Kit (#65057K)**  
 Each kit contains one shelf and four mounting clips.



COMMERCIAL FREEZERS & REFRIGERATORS

