

CM411L7



33.5" x 19.25" x 21.38" (H x W x D)

Commercially listed 20" wide counter height refrigerator-freezer with a lock, white exterior

Highlights:

Slim 20" width is ideal for any setting

ETL-S listed for commercial use

Factory installed lock provides security you can count on

Includes a hospital grade cord with a 'green dot' plug

Product Features:

Commercially listed	ETL-S listed to NSF standards for commercial use
Slim 20" width	Full 4.1 cu.ft. capacity inside conveniently slim footprint
Fully finished white cabinet	Allows the unit to be used freestanding
Factory installed lock	Top-mounted for convenient security
Reversible door	Keep your options flexible with a reversible door that is easy to switch when your arrangement changes
Hospital grade cord with 'green dot' plug	Secure three-pronged cord for added unit safety
Manual defrost	Efficient performance with reliable temperature stability
Adjustable shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup
Crisper drawer	Get the longest life and best taste out of produce by storing greens in a bottom crisper

CM411L7 Specifications:

Overview	
Height	33.5"
Height to Hinge Cap	34.0"
Width	19.25"
Depth	21.38"
Depth with Handle	23.0"
Depth with door at 90°	39.5"
Capacity	4.1 cu.ft.
Defrost Type	Manual
Door	White
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Amps	1.4
Voltage/Frequency	115 V AC/60 Hz
Weight	57.0 lbs.
Shipping Weight	80.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	28.75"
Refrigerator - Interior Width	15.75"
Refrigerator - Interior Depth	17.75"
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	2
Adjustable Shelves	Yes
Interior Light	Yes
Thermostat Type	Dial
Freon	R134a
Freon Amount	1.75

High Side PSI	205.0
Low Side PSI	103.0
Level Legs	2
Wheels	2

