SAFETY DATA SHEET

Issuing Date No data available Revision Date 25-Nov-2014 Revision Number 1



The supplier identified below generated this SDS using the UL SDS template. UL did not test, certify, or approve the substance described in this SDS, and all information in this SDS was provided by the supplier or was reproduced from publically available regulatory data sources. UL makes no representations or warranties regarding the completeness or accuracy of the information in this SDS and disclaims all liability in connection with the use of this information or the substance described in this SDS. The layout, appearance and format of this SDS is © 2014 UL LLC. All rights reserved.

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product identifier

Product Name EFP Furniture Polish (9731)

Other means of identification

Synonyms None

Recommended use of the chemical and restrictions on use

Recommended Use Furniture polish

Uses advised against No information available

Details of the supplier of the safety data sheet

Supplier NameVENUS LABORATORIESSupplier Address111 S ROHLWING ROAD

ADDISO N IL 60101 US

Supplier Phone Number Phone:800-592-1900
Emergency telephone number Chemtrec: 800-424-9300

2. HAZARDS IDENTIFICATION

Classification

This chemical is not considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

GHS Label elements, including precautionary statements

Emergency Overview								
'	'							



The product contains no substances which at their given concentration, are considered to be hazardous to health

Appearance Beige Physical State Emulsion Liquid Odor Citrus

Precautionary Statements - Prevention

Obtain special instructions before use

Precautionary Statements - Response

None

Precautionary Statements - Storage

None

Precautionary Statements - Disposal

None

Hazards not otherwise classified (HNOC)

Not applicable

Unknown Toxicity

6.65% of the mixture consists of ingredient(s) of unknown toxicity

Other information

May cause slight eye irritation

Interactions with Other Chemicals

No information available.

3. COMPOSITION/INFORMATION ON INGREDIENTS

. The product contains no substances which at their given concentration, are considered to be hazardous to health.

4. FIRST AID MEASURES

First aid measures

Eye Contact Rinse immediately with plenty of water, also under the eyelids, for at least 15

minutes. Keep eye wide open while rinsing. Remove contact lenses, if present and

If irritation persists consult a doctor/physician.

Skin Contact Wash off immediately with soap and plenty of water for at least 15 minutes. May

cause an allergic skin reaction. In the case of skin irritation or allergic reactions

see a physician.

Inhalation Remove to fresh air.

Ingestion Rinse mouth immediately and drink plenty of water. Never give anything by mouth

to an unconscious person.

Most important symptoms and effects, both acute and delayed

Most Important Symptoms and No information available.

Effects



Indication of any immediate medical attention and special treatment needed

Notes to Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

CAUTION: Use of water spray when fighting fire may be inefficient.

Specific Hazards Arising from the Chemical

No information available.

Uniform Fire Code Sensitizer: Liquid

Hazardous Combustion Products

Carbon oxides.

Explosion Data

Sensitivity to Mechanical Impact No.

Sensitivity to Static Discharge No.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal Precautions Avoid contact with eyes.

Environmental Precautions

Environmental Precautions Refer to protective measures listed in Sections 7 and 8.

Methods and material for containment and cleaning up

Methods for Containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning upSoak up with inert absorbent material. Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Handling Handle in accordance with good industrial hygiene and safety practice. Avoid contact with

eves.

Conditions for safe storage, including any incompatibilities

Storage Keep container tightly closed.

Incompatible Products None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure GuidelinesThis product, as supplied, does not contain any hazardous materials with occupational

exposure limits established by the region specific regulatory bodies

Appropriate engineering controls

Engineering Measures Showers

Eyewash stations Ventilation systems

Individual protection measures, such as personal protective equipment

Eye/Face Protection No special protective equipment required.

Skin and Body ProtectionNo special protective equipment required.

Respiratory ProtectionNo protective equipment is needed under normal use conditions. If exposure limits are

exceeded or irritation is experienced, ventilation and evacuation may be required.

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical and Chemical Properties

Physical StateEmulsion LiquidAppearanceThick OpaqueOdorCitrus

Color Pale Beige Odor Threshold No information available

Propert Values Remarks Method

None known y pH Melting / freezing point No data available None known 212°F Boiling point / boiling range None known Flash Point 94° C / 201° F None known No data available **Evaporation Rate** None known No data available None known Flammability (solid, gas)

Flammability Limit in Air

Upper flammability limit No data available



No data available Lower flammability limit Vapor pressure No data available None known Vapor density No data available None known **Specific Gravity** 1.02 None known Water Solubility Soluble in water None known Solubility in other solvents No data available None known Partition coefficient: n-octanol/waterNo data available None known **Autoignition temperature** No data available None known **Decomposition temperature** No data available None known No data available Kinematic viscosity None known No data available Dynamic viscosity None known No data available **Explosive properties**

No data available

Other Information

Oxidizing Properties

Softening PointNo data availableVOC Content (%)No data availableParticle SizeNo data available

Particle Size Distribution

10. STABILITY AND REACTIVITY

Reactivity

No data available.

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Hazardous Polymerization

Hazardous polymerization does not occur.

Conditions to avoid

None known based on information supplied.

Incompatible materials

None known based on information supplied.

Hazardous Decomposition Products

Carbon oxides.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Inhalation Specific test data for the substance or mixture is not available. No irritation expected.

Eye Contact Specific test data for the substance or mixture is not available. No irritation expected.

Skin Contact Specific test data for the substance or mixture is not available. No irritation expected.

Ingestion Specific test data for the substance or mixture is not available. No irritation expected.



Page 5/9

Component Information

Information on toxicological effects

Symptoms No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No information available.

Mutagenic Effects No information available.

Carcinogenicity Contains no ingredient listed as a carcinogen.

Reproductive Toxicity No information available.

STOT - single exposure No information available.

STOT - repeated exposure No information available.

Chronic Toxicity No known effect based on information supplied.

Target Organ Effects None known.

Aspiration Hazard No information available.

Numerical measures of toxicity Product Information

The following values are calculated based on chapter 3.1 of the GHS document

Not applicable

12. ECOLOGICAL INFORMATION

Ecotoxicity

The environmental impact of this product has not been fully investigated.

Persistence and Degradability

No information available.

Bioaccumulation

No information available

Other adverse effects

No information available.

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal methods This material, as supplied, is not a hazardous waste according to Federal regulations (40

CFR 261). This material could become a hazardous waste if it is mixed with or otherwise comes in contact with a hazardous waste, if chemical additions are made to this material, or if the material is processed or otherwise altered. Consult 40 CFR 261 to determine whether the altered material is a hazardous waste. Consult the appropriate state, regional, or local

regulations for additional requirements.

Contaminated Packaging Dispose of contents/containers in accordance with local regulations.

California Hazardous Waste Codes 331

14. TRANSPORT INFORMATION

DOT NOT REGULATED

Proper Shipping Name NON REGULATED

Hazard Class N/A

TDG Not regulated

MEX Not regulated

ICAO Not regulated

IATA Not regulated

Proper Shipping Name NON REGULATED

Hazard Class N/A

IMDG/IMO Not regulated

Hazard Class N/A

RID Not regulated

ADR Not regulated

ADN Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA Complies

DSL All components are listed either on the DSL or NDSL.

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations



SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute Health Hazard

Chronic Health Hazard

No
Fire Hazard

No
Sudden release of pressure hazard

No
Reactive Hazard

No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product does not contains the following Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

.

Chemical Name	New Jersey	Massachusetts	Pennsylvania	Rhode Island	Illinois
Phenoxyethanol 122-99-6	X		Χ	Х	X
Sodium hydroxide 1310-73-2	Х	X	Χ	Χ	

International Regulations

Canada

WHMIS Hazard Class

Non-controlled

Revision Date

		16. OTHER INFORMATION					
NFPA	Health Hazards 1	Flammability 0	Instability 0	Physical and Chemical Hazards			
HMIS	Health Hazards 1	Flammability 0	Physical Hazard 0	Personal Protection			

1-800-572-6501 25-Nov-2014

Revision Note No information available



Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet

