

CM411LBI7FR



33.5" x 19.25" x 21.38" (H x W x D)

Commercially listed 20" wide built-in undercounter refrigerator-freezer with a lock, custom door for slide-in panels and white exterior

Highlights:

ETL-S listed for commercial use

Flexible design allows built-in or freestanding use in 20" wide spaces

Factory installed lock provides security you can count on

Slide your own panel into the door frame for an easy custom look

Product Features:

Commercially listed	ETL-S listed to NSF standards for commercial use
Slim 20" width	Full 4.1 cu.ft. capacity inside conveniently slim footprint
Built-in capable	Make the best use of space by installing your appliance under the counter
Fully finished white cabinet	Allows the unit to be used freestanding
Stainless steel door frame	Two-piece "U"-shaped door frame accepts slide-in custom panels (panel size: 19 1/4" W x 31 1/4" H at up to 1/4" thick)
Reversible door	User reversible door swing
Hospital grade cord with 'green dot' plug	Secure three-pronged cord for added unit safety
Manual defrost	Efficient performance with reliable temperature stability
Adjustable shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup

CM411LBI7FR Specifications:

Overview	
Height	33.5"
Height to Hinge Cap	34.0"
Width	19.25"
Depth	21.38"
Depth with door at 90°	39.5"
Capacity	4.1 cu.ft.
Defrost Type	Manual
Door	Panel-Ready
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Amps	1.4
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs.
Shipping Weight	85.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	28.75"
Refrigerator - Interior Width	15.75"
Refrigerator - Interior Depth	17.75"
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	2
Adjustable Shelves	Yes
Interior Light	Yes
Thermostat Type	Dial
Freon	R134a
Freon Amount	1.75
High Side PSI	205.0

Low Side PSI

Level Legs

Wheels

