

SAFETY DATA SHEET

Issuing Date No data available

Revision Date 24-Nov-2014

Revision Number 1

The supplier identified below generated this SDS using the UL SDS template. UL did not test, certify, or approve the substance described in this SDS, and all information in this SDS was provided by the supplier or was reproduced from publicly available regulatory data sources. UL makes no representations or warranties regarding the completeness or accuracy of the information in this SDS and disclaims all liability in connection with the use of this information or the substance described in this SDS. The layout, appearance and format of this SDS is © 2014 UL LLC. All rights reserved.

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product identifier

Product Name: Concentrate Window Cleaner Lavender (9963)

Other means of identification

Synonyms None

Recommended use of the chemical and restrictions on use

Recommended Use Glass Cleaner - Non-Aerosol

Uses advised against No information available

Details of the supplier of the safety data sheet

Supplier Name VENUS LABORATORIES

Supplier Address
111 S ROHLWING ROAD
ADDISON IL
60101
US

Supplier Phone Number Phone:800-592-1900

Emergency telephone number Chemtrec: 800-424-9300

2. HAZARDS IDENTIFICATION

Classification

This chemical is not considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

GHS Label elements, including precautionary statements

Emergency Overview

The product contains no substances which at their given concentration, are considered to be hazardous to health

Appearance Clear

Physical State Liquid

Odor Lavender

Precautionary Statements - Prevention

Obtain special instructions before use

Precautionary Statements - Response

None

Precautionary Statements - Storage

None

Precautionary Statements - Disposal

None

Hazards not otherwise classified (HNOC)

Not applicable

Unknown Toxicity

1.25% of the mixture consists of ingredient(s) of unknown toxicity

Other informationHarmful to aquatic life with long lasting effects
May cause slight eye irritation**Interactions with Other Chemicals**

Use of alcoholic beverages may enhance toxic effects.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
Ethyl alcohol	64-17-5	1 - 5	*

*The exact percentage (concentration) of composition has been withheld as a trade secret

4. FIRST AID MEASURES**First aid measures****Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Keep eye wide open while rinsing. Remove contact lenses, if present and if irritation persists consult a doctor/physician.

Skin Contact

Wash off immediately with soap and plenty of water for at least 15 minutes. May cause an allergic skin reaction. In the case of skin irritation or allergic reactions see a physician.

Inhalation

Remove to fresh air.

Ingestion

Rinse mouth immediately and drink plenty of water. Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed**Most Important Symptoms and Effects**

No information available.

Indication of any immediate medical attention and special treatment needed**Notes to Physician**

Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

CAUTION: Use of water spray when fighting fire may be inefficient.

Specific Hazards Arising from the Chemical

No information available.

Uniform Fire Code

Combustible Liquid: III-B

Hazardous Combustion Products

Carbon oxides.

Explosion Data

Sensitivity to Mechanical Impact No.

Sensitivity to Static Discharge No.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal Precautions

Avoid contact with eyes.

Environmental Precautions

Environmental Precautions

Refer to protective measures listed in Sections 7 and 8.

Methods and material for containment and cleaning up

Methods for Containment

Prevent further leakage or spillage if safe to do so.

Methods for cleaning up

Soak up with inert absorbent material. Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Handling

Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Do not eat, drink or smoke when using this product.

Conditions for safe storage, including any incompatibilities

Storage

Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible Products

None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Ethyl alcohol 64-17-5	STEL: 1000 ppm	TWA: 1000 ppm TWA: 1900 mg/m ³ (vacated) TWA: 1000 ppm (vacated) TWA: 1900 mg/m ³	IDLH: 3300 ppm 10% LEL TWA: 1000 ppm TWA: 1900 mg/m ³

ACGIH TLV: American Conference of Governmental Industrial Hygienists - Threshold Limit Value OSHA PEL: Occupational Safety and Health Administration - Permissible Exposure Limits Immediately Dangerous to Life or Health

Other Exposure Guidelines Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992) See section 15 for national exposure control parameters

Appropriate engineering controls

Engineering Measures Showers
Eyewash stations
Ventilation systems

Individual protection measures, such as personal protective equipment

Eye/Face Protection If splashes are likely to occur: Wear safety glasses with side shields (or goggles). None required for consumer use.

Skin and Body Protection No special protective equipment required.

Respiratory Protection No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice. Take off contaminated clothing and wash before reuse.
Do not eat, drink or smoke when using this product.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical and Chemical Properties

Physical State	Liquid	Odor	Lavender
Appearance	Clear		
Color	No information available		
Odor Threshold	No information available		

Property	Values	Remarks/_Method
pH	3	None known
Melting / freezing point	No data available	None known
Boiling point / boiling range	No data available	None known
Flash Point	94° C / 201° F	None known
Evaporation Rate	No data available	None known
Flammability (solid, gas)	No data available	None known
Flammability Limit in Air		
Upper flammability limit	No data available	
Lower flammability limit	No data available	
Vapor pressure	No data available	None known
Vapor density	No data available	None known
Specific Gravity Water	0.99	None known
Solubility	Soluble in water	None known
Solubility in other solvents	No data available	None known
Partition coefficient: n-octanol/water	No data available	None known

Autoignition temperature Decomposition temperature Kinematic viscosity Dynamic viscosity Explosive properties Oxidizing Properties	No data available No data available No data available No data available No data available No data available	None known None known None known None known
Other Information		
Softening Point VOC Content (%) Particle Size	No data available No data available No data available	
Particle Size Distribution		

10. STABILITY AND REACTIVITY

Reactivity

No data available.

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Hazardous Polymerization

Hazardous polymerization does not occur.

Conditions to avoid

None known based on information supplied.

Incompatible materials

None known based on information supplied.

Hazardous Decomposition Products

Carbon oxides.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Inhalation

Specific test data for the substance or mixture is not available.

Eye Contact

Specific test data for the substance or mixture is not available. No adverse reaction expected

Skin Contact

Specific test data for the substance or mixture is not available. Not expected to be a skin irritant based on components. Prolonged contact may cause redness and irritation.

Ingestion

Specific test data for the substance or mixture is not available.

Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Ethyl alcohol 64-17-5	-	-	= 124.7 mg/L (Rat) 4 h

Information on toxicological effects

Symptoms

No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No information available.

Mutagenic Effects No information available.

Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical Name	ACGIH	IARC	NTP	OSHA
Ethyl alcohol 64-17-5	A3	Group 1	Known	X

ACGIH (American Conference of Governmental Industrial Hygienists)

A3 - Animal Carcinogen

IARC (International Agency for Research on Cancer)

Group 1 - Carcinogenic to Humans

NTP (National Toxicology Program)

Known - Known Carcinogen

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Reproductive Toxicity No information available.

STOT - single exposure No information available.

STOT - repeated exposure No information available.

Chronic Toxicity

No known effect based on information supplied. Ethanol has been shown to be a reproductive toxin only when consumed as an alcoholic beverage. Ethanol has been shown to be carcinogenic in long-term studies only when consumed as alcoholic beverage.

Target Organ Effects Blood. Central Nervous System (CNS). Eyes. Liver. Reproductive System. Respiratory system. Skin.

Aspiration Hazard No information available.

Numerical measures of toxicity_Product Information

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (inhalation-dust/mist)

4,988.00 mg/l

12. ECOLOGICAL INFORMATION

Ecotoxicity

Harmful to aquatic life with long lasting effects.

Chemical Name	Toxicity to Algae	Toxicity to Fish	Toxicity to Microorganisms	Daphnia Magna (Water Flea)
Ethyl alcohol 64-17-5		96h LC50: > 100 mg/L (Pimephales promelas) 96h LC50: 13400 - 15100 mg/L (Pimephales promelas) 96h LC50: 12.0 - 16.0 mL/L (Oncorhynchus mykiss)	EC50 = 34634 mg/L 30 min EC50 = 35470 mg/L 5 min	48h LC50: 9268 - 14221 mg/L 48h EC50: = 2 mg/ L 24h EC50: = 10800 mg/L

Persistence and Degradability

No information available.

Bioaccumulation

Chemical Name	Log Pow
Ethyl alcohol 64-17-5	-0.32

Other adverse effects
No information available.

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal methods This material, as supplied, is not a hazardous waste according to Federal regulations (40 CFR 261). This material could become a hazardous waste if it is mixed with or otherwise comes in contact with a hazardous waste, if chemical additions are made to this material, or if the material is processed or otherwise altered. Consult 40 CFR 261 to determine whether the altered material is a hazardous waste. Consult the appropriate state, regional, or local regulations for additional requirements.

Contaminated Packaging Dispose of contents/containers in accordance with local regulations.

California Hazardous Waste Codes 561

This product contains one or more substances that are listed with the State of California as a hazardous waste.

Chemical Name	California Hazardous Waste
Ethyl alcohol 64-17-5	Toxic Ignitable

14. TRANSPORT INFORMATION

1. **DQT** NOT REGULATED
Proper Shipping Name NON REGULATED
Hazard Class N/A
- TDG** Not regulated
- MEX** Not regulated
- ICAO** Not regulated
- IATA** Not regulated
Proper Shipping Name NON REGULATED
Hazard Class N/A
- IMDG/IMO** Not regulated
Hazard Class N/A
- RID** Not regulated
- ADR** Not regulated
- ADN** Not regulated

International Inventories

15. REGULATORY INFORMATION

1. **TSCA** Complies
DSL All components are listed either on the DSL or NDSL.

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
 DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute Health Hazard	No
Chronic Health Hazard	No
Fire Hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product contains the following Proposition 65 chemicals. Ethyl alcohol is only a considered a Proposition 65 developmental hazard when it is ingested as an alcoholic beverage.

Chemical Name	California Proposition 65
Ethyl alcohol - 64-17-5	Carcinogen Developmental

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania	Rhode Island	Illinois
Ethyl alcohol 64-17-5		X			

International Regulations

Mexico

National occupational exposure limits

Mexico - Occupational Exposure Limits - Carcinogens

Canada

WHMIS Hazard Class

Non-controlled

16. OTHER INFORMATION

NFPA	Health Hazards 1	Flammability 1	Instability 0	Physical and Chemical Hazards -
HMIS	Health Hazards 1	Flammability 1		
Physical Hazard 0	Personal Protection		X	

Revision Date	24-Nov-2014
Revision Note	No information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet