

CM411LBI7SSHADA



32" x 19.25" x 21.38" (H x W x D)

Commercially listed ADA compliant 20" wide built-in refrigerator-freezer with a lock, stainless steel door, horizontal handle and white cabinet

Highlights:

ETL-S listed for commercial use

32" height fits under lower ADA compliant counters

Flexible design allows built-in or freestanding use in 20" wide spaces

Professional look with a durable stainless steel wrapped door and sleek horizontal handle

Product Features:

| | |
|---|--|
| Commercially listed | ETL-S listed to NSF standards for commercial use |
| ADA compliant | 32" high to fit under lower ADA compliant counters |
| Built-in capable | Make the best use of space by installing your appliance under the counter |
| Slim 20" width | Full 4.1 cu.ft. capacity inside conveniently slim footprint |
| Fully finished white cabinet | Allows the unit to be used freestanding |
| Stainless steel wrapped door | Durable 304 grade wrapping |
| Professional horizontal handle | Thin 14mm diameter on stainless steel handle, mounted horizontally on the door |
| Factory installed lock | Top-mounted for convenient security |
| Hospital grade cord with 'green dot' plug | Secure three-pronged cord for added unit safety |

CM411LBI7SSHADA Specifications:

| Overview | |
|--------------------------------|--------------------|
| Height | 32.0" |
| Height to Hinge Cap | 32.5" |
| Width | 19.25" |
| Depth | 21.38" |
| Depth with door at 90° | 39.5" |
| Capacity | 4.1 cu.ft. |
| Defrost Type | Manual |
| Door | Stainless Steel |
| Cabinet | White |
| US Electrical Safety | ETL |
| Canadian Electrical Safety | ETL-C |
| Sanitation | ETL-S |
| Amps | 1.4 |
| Voltage/Frequency | 115 V AC/60 Hz |
| Weight | 64.0 lbs. |
| Shipping Weight | 85.0 lbs. |
| Parts & Labor Warranty | 1 Year |
| Compressor Warranty | 5 Years |
| Refrigerator-Freezer | |
| Door Swing | RHD |
| Reversible | Factory Reversible |
| Crisper Qty | 1 |
| Crisper Finish | Transparent |
| Crisper Cover | Glass |
| Refrigerator - Interior Height | 28.75" |
| Refrigerator - Interior Width | 15.75" |
| Refrigerator - Interior Depth | 17.75" |
| Refrigerator - Shelf Type | Wire |
| Refrigerator - Shelf Qty | 2 |
| Adjustable Shelves | Yes |
| Interior Light | Yes |
| Thermostat Type | Dial |
| Freon | R134a |
| Freon Amount | 1.75 |
| High Side PSI | 205.0 |

Low Side PSI

Level Legs

Wheels

