

# ALB753BIF



32" x 23.63" x 23.5" (H x W x D)

ADA compliant built-in undercounter all-refrigerator for general purpose use, auto defrost w/integrated door frame for custom panel overlays and black cabinet

## Highlights:

Flexible design allows built-in or freestanding use in 24" spaces

32" height for use under lower ADA compliant counters

Automatic defrost ensures minimum user maintenance

Customizable door front accepts full overlay panels for a seamless look that can blend into cabinetry

## Product Features:

ADA Compliant	32 inch height is designed to fit under ADA compliant counters
Slim undercounter dimensions	Less than 24 inches wide, with a generous 5.5 c.f. of storage capacity
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinetry
Fully finished black cabinet	Allows the unit to be used freestanding
Integrated door frame	Customize the front by mounting an overlay panel over the door; seamless look can blend into other cabinetry with no exposed frame. Handle not included (panel size: 23 5/16" W x 28 1/4" H and at least 3/4" thick)
Automatic defrost	Reduced user maintenance with automatic defrost operation
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior
One piece interior liner	Simple cleanup with a seamless liner that won't hold a mess in hidden crevices
Adjustable glass shelves	Rearrange the refrigerator space to fit any sized item or remove shelves for simple cleanup

**ALB753BIF Specifications:**

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Depth with door at 90°	45.63"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Panel-Ready
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Energy Usage/Year	405.0kWh/year
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	107.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8oz.
High Side PSI	285.0
Low Side PSI	88.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	26.25"
Interior Width	21.0"
Interior Depth	17.75"
Compressor Step Height	5.5"

Compressor Step Width  
Compressor Step Depth

