

CT66B



33.25" x 23.63" x 23.5" (H x W x D)

Freestanding refrigerator-freezer for general purpose use, with dual evaporator cooling, cycle defrost, and black exterior

Highlights:

Over 5 cu.ft. of storage capacity in a perfectly sized 24" footprint

Includes adjustable glass shelves for spill-proof storage

Improved temperature performance with our unique dual evaporator cooling

Zero degree freezer compartment

Product Features:

100% CFC free	Environmentally friendly design without ozone-damaging chemicals
Dual evaporator	Our unique and efficient design separately cools the refrigerator while maintaining zero degrees in the freezer with two evaporators
Door storage	Store tall bottles and condiments right on the door for convenient access
Fruit and vegetable crisper	Get the longest life and best taste out of produce by storing it in a convenient slide drawer
Adjustable glass shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Interior light	Automatically illuminates when you open the door
Adjustable thermostat	Dial thermostat located inside for easy temperature management
Thin-line design	Our unique 24" wide models offer full capacity in a slim fit
Zero degree freezer	Static manual defrost freezer section offers more stability

CT66B Specifications:

Overview	
Height	33.25"
Width	23.63"
Depth	23.5"
Depth with Handle	24.5"
Depth with door at 90°	45.25"
Capacity	5.1 cu.ft.
Defrost Type	Cycle
Door	Black
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	107.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	19.5"
Refrigerator - Interior Width	20.5"
Refrigerator - Interior Depth	17.0"
Refrigerator - Shelf Type	Glass
Refrigerator - Shelf Qty	3
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	5.0"
Freezer - Interior Width	19.0"
Freezer - Interior Depth	11.5"
Adjustable Shelves	Yes
Interior Light	Yes
Thermostat Type	Dial
Freon	R134a
Freon Amount	2.6

High Side PSI	285.0
Low Side PSI	70.0
Level Legs	2
Compressor Step Height	7.0"
Compressor Step Width	20.5"
Compressor Step Depth	5.0"

