

FF511L7SSHV



33.5" x 19.25" x 21.38" (H x W x D)

Commercially listed 20" wide counter height all-refrigerator, auto defrost with a lock, stainless steel door, thin handle, and white cabinet

Highlights:

ETL-S listed for commercial use

Counter height all-refrigerator offers full 4.1 cu.ft. capacity

Factory installed lock provides security you can count on

Slim 20" width is ideal for any setting

Product Features:

Commercially listed	ETL-S listed to NSF standards for commercial use
Slim 20" width	Full 4.1 cu.ft. capacity inside conveniently slim footprint
Fully finished white cabinet	Allows the unit to be used freestanding
Factory installed lock	Top-mounted for convenient security
Stainless steel wrapped door	Durable 304 grade wrapping
Professional handle	Thin 14mm diameter on vertical stainless steel handle
Automatic defrost	Reduced maintenance with auto defrost system
Adjustable shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup
Hospital grade cord with 'green dot' plug	Secure three-pronged cord for added unit safety

FF511L7SSHV Specifications:

Overview	
Height	33.5"
Height to Hinge Cap	34.0"
Width	19.25"
Depth	21.38"
Depth with door at 90°	39.5"
Capacity	4.1 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Energy Usage/Year	406.0kWh/year
Amps	1.4
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs.
Shipping Weight	85.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Shelf Type	Wire
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.75oz.
High Side PSI	205.0
Low Side PSI	103.0
Level Legs Qty	2
Interior Light	Yes
Dimensions	
Interior Height	28.5"

Interior Width	15.75"
Interior Depth	18.0"
Compressor Step Height	8.0"
Compressor Step Width	17.0"
Compressor Step Depth	6.75"

