

# FF511LADA



32" x 19.25" x 21.38" (H x W x D)

ADA Compliant 20" wide counter height all-refrigerator for general purpose use, auto defrost with a lock and white exterior

### Highlights:

32" height for use in ADA compliant settings

Freestanding all-refrigerator offers full 4.1 cu.ft. capacity

Factory installed lock provides security you can count on

Save time and energy with low maintenance automatic defrost

### Product Features:

ADA compliant	32" high meets ADA guidelines
Slim 20" width	Full 4.1 cu.ft. capacity inside conveniently slim footprint
Fully finished white cabinet	Allows the unit to be used freestanding
Factory installed lock	Top-mounted for convenient security
Reversible door	Keep your options flexible with a reversible door that is easy to switch when your arrangement changes
Automatic defrost	Reduced maintenance with auto defrost system
Adjustable shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup
Crisper drawer	Get the longest life and best taste out of produce by storing greens in a bottom crisper
Interior light	Turn the light on and off with a convenient rocker switch

**FF511LADA Specifications:**

Overview	
Height	32.0"
Height to Hinge Cap	32.56"
Width	19.25"
Depth	21.38"
Depth with Handle	23.0"
Depth with door at 90°	39.5"
Capacity	4.1 cu.ft.
Defrost Type	Automatic
Door	White
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Energy Usage/Year	406.0kWh/year
Amps	1.4
Voltage/Frequency	115 V AC/60 Hz
Weight	57.0 lbs.
Shipping Weight	80.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Shelf Type	Wire
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.75
High Side PSI	205.0
Low Side PSI	103.0
Level Legs Qty	2
Interior Light	Yes
Dimensions	
Interior Height	28.5"

Interior Width	15.75"
Interior Depth	18.0"
Compressor Step Height	8.0"
Compressor Step Width	17.0"
Compressor Step Depth	6.75"

