

# FF511LBI7IF



33.5" x 19.25" x 21.38" (H x W x D)

Commercially listed 20" wide built-in undercounter all-refrigerator, auto defrost with a lock and integrated door frame for full overlay panels

### Highlights:

ETL-S listed for commercial use

Flexible design allows built-in or freestanding use in 20" wide spaces

Factory installed lock provides security you can count on

Save time and energy with low maintenance automatic defrost

### Product Features:

Commercially listed	ETL-S listed to NSF standards for commercial use
Slim 20" width	Full 4.1 cu.ft. capacity inside conveniently slim footprint
Built-in capable	Make the best use of space by installing your appliance under the counter
Fully finished white cabinet	Allows the unit to be used freestanding
Factory installed lock	Top-mounted for convenient security
Integrated door frame	Stainless steel door frame accepts overlay panels for users to create a custom look over the front (panel size: 19 1/2" W x 31 1/2" H and at least 3/4" thick)
Hospital grade cord with 'green dot' plug	Secure three-pronged cord for added unit safety
Automatic defrost	Reduced maintenance with auto defrost system
Adjustable shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup

## FF511LBI7IF Specifications:

Overview	
Height	33.5"
Height to Hinge Cap	34.0"
Width	19.25"
Depth	21.38"
Depth with door at 90°	39.5"
Capacity	4.1 cu.ft.
Defrost Type	Automatic
Door	Panel-Ready
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Energy Usage/Year	406.0kWh/year
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs.
Shipping Weight	85.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Shelf Type	Wire
Shelf Qty	2
Full Door Shelf Qty	1
Half Door Shelf Qty	2
Adjustable Shelves	Yes
Can Storage	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.9oz.
High Side PSI	250.0
Low Side PSI	110.0
Level Legs Qty	2

Interior Light	Yes
Dimensions	
Interior Height	28.5"
Interior Width	15.75"
Interior Depth	18.0"
Compressor Step Height	8.0"
Compressor Step Width	16.5"
Compressor Step Depth	5.5"

