

FF511LBI7SSHVADA



32" x 19.25" x 21.38" (H x W x D)

Commercially listed ADA Compliant 20" wide built-in undercounter all-refrigerator, auto defrost w/lock, stainless steel door, thin handle and white cabinet

Highlights:

ETL-S listed for commercial use

Flexible design allows built-in or freestanding use in 20" wide spaces

32" height fits under lower ADA compliant counters

Factory installed lock provides security you can count on

Product Features:

Slim 20" width	Full 4.1 cu.ft. capacity inside conveniently slim footprint
ADA compliant	32" high to fit under lower ADA compliant counters
Commercially listed	ETL-S listed to NSF standards for commercial use
Built-in capable	Make the best use of space by installing your appliance under the counter
Factory installed lock	Top-mounted for convenient security
Stainless steel wrapped door	Durable 304 grade wrapping
Professional handle	Thin 14mm diameter on vertical stainless steel handle
Fully finished white cabinet	Allows the unit to be used freestanding
Automatic defrost	Reduced maintenance with auto defrost system

FF511LBI7SSHVADA Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.5"
Width	19.25"
Depth	21.38"
Depth with door at 90°	39.5"
Capacity	4.1 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Energy Usage/Year	406.0kWh/year
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs.
Shipping Weight	85.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Shelf Type	Wire
Shelf Qty	2
Full Door Shelf Qty	1
Half Door Shelf Qty	2
Adjustable Shelves	Yes
Can Storage	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.9oz.
High Side PSI	250.0
Low Side PSI	110.0
Level Legs Qty	2

Interior Light Yes

Dimensions	
Interior Height	28.5"
Interior Width	15.75"
Interior Depth	18.0"
Compressor Step Height	8.0"
Compressor Step Width	16.5"
Compressor Step Depth	5.5"

