

# FF521BL7DPLADA



32" x 19.25" x 21.38" (H x W x D)

Commercially listed ADA Compliant 20" wide counter height all-refrigerator, auto defrost with a lock, diamond plate wrapped door and black cabinet

### Highlights:

ETL-S listed for commercial use

32" height for use in ADA compliant settings

Industrial look with a textured diamond wrapped door

Slim 20" width is ideal for any setting

### Product Features:

ADA compliant	32" high meets ADA guidelines
Commercially listed	ETL-S listed to NSF standards for commercial use
Slim 20" width	Full 4.1 cu.ft. capacity inside conveniently slim footprint
Fully finished black cabinet	Allows the unit to be used freestanding
Factory installed lock	Top-mounted for convenient security
Diamond plate door	Unique textured finish offers modern industrial look
Professional towel bar handle	Curved towel bar design in polished stainless steel
Automatic defrost	Reduced maintenance with auto defrost system
Hospital grade cord with 'green dot' plug	Secure three-pronged cord for added unit safety

**FF521BL7DPLADA Specifications:**

Overview	
Height	32.0"
Height to Hinge Cap	32.5"
Width	19.25"
Depth	21.38"
Depth with door at 90°	39.5"
Capacity	4.1 cu.ft.
Defrost Type	Automatic
Door	Diamond Plate
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Energy Usage/Year	406.0kWh/year
Amps	1.4
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs.
Shipping Weight	85.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.75oz.
High Side PSI	205.0
Low Side PSI	103.0
Level Legs Qty	2
Interior Light	Yes
Dimensions	
Interior Height	28.5"

Interior Width	15.75"
Interior Depth	18.0"
Compressor Step Height	8.0"
Compressor Step Width	17.0"
Compressor Step Depth	6.75"

