

FF6BBI7



33.25" x 23.63" x 23.5" (H x W x D)

Commercially listed built-in undercounter all-refrigerator for general purpose use, with automatic defrost operation and black exterior

Highlights:

Flexible design allows built-in or freestanding use in 24" spaces

Automatic defrost saves you time and maintenance

Includes adjustable glass shelves for flexible storage

Commercially approved for use in foodservice establishments

Product Features:

Commercially approved	ETL-S listed to NSF-7 commercial standards
Slim undercounter dimensions	Our unique 24" wide models offer full capacity in a slim fit
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Fully finished black cabinet	Allows the refrigerator to be used freestanding
Automatic defrost	Reduced maintenance with auto defrost system
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior
One piece interior liner	Enjoy easy clean-up with a seamless liner that won't hold a mess in hidden crevices
Adjustable glass shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Crisper	Get the longest life and best taste out of produce by storing it in a convenient slide drawer

FF6BBI7 Specifications:

Overview	
Height	33.25"
Height to Hinge Cap	34.5"
Width	23.63"
Depth	23.5"
Depth with Handle	25.13"
Depth with door at 90°	46.13"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Black
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Shipping Weight	104.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Opaque
Crisper Cover	Glass
Shelf Type	Glass
Shelf Qty	3
Full Door Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"

Interior Depth	17.0"
Compressor Step Height	7.0"
Compressor Step Width	20.0"
Compressor Step Depth	6.0"

