

FF6BIIFADA



32" x 23.63" x 23.5" (H x W x D)

ADA compliant all-refrigerator for built-in general purpose use, auto defrost w/integrated door frame for overlay panels and white cabinet

Highlights:

- 32 inch height fits under lower ADA compliant counters
- Customizable door front accepts full overlay panels for a seamless look that can blend into cabinetry
- Flexible design allows built-in or freestanding use in 24" spaces
- Automatic defrost ensures minimum user maintenance

Product Features:

ADA compliant	32 inch height fits under standard ADA counters
Slim undercounter dimensions	Less than 24 inches wide with a full 5.5 c.f. capacity
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Fully finished white cabinet	Allows the unit to be used freestanding
Integrated door frame	Customize the front by mounting an overlay panel over the door; seamless look can blend into other cabinetry with no exposed frame. Handle not included (panel size: 23 5/16" W x 28 1/4" H and at least 3/4" thick)
Automatic defrost	Reduced maintenance with auto defrost system
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior
One piece interior liner	Easy clean-up with a seamless liner that won't hold a mess in hidden crevices
Adjustable shelves	Rearrange the refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up

FF6BIIFADA Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Depth with door at 90°	45.63"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Panel-Ready
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	108.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Opaque
Crisper Cover	Glass
Shelf Type	Wire
Shelf Qty	3
Full Door Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8oz.
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"

Interior Width	20.0"
Interior Depth	17.5"
Compressor Step Height	7.0"
Compressor Step Width	20.0"
Compressor Step Depth	6.0"

