

FF521BLBISSHADA



32" x 19.25" x 21.38" (H x W x D)

ADA Compliant 20" wide built-in undercounter all-refrigerator for general purpose use, auto defrost with a lock, SS door, horizontal handle and black cabinet

Highlights:

Flexible design allows built-in or freestanding use in 20" wide spaces

32" height for use in ADA compliant settings

Factory installed lock provides security you can count on

Professional look with a durable stainless steel wrapped door and sleek horizontal handle

Product Features:

Slim 20" width	Full 4.1 cu.ft. capacity inside conveniently slim footprint
ADA compliant	32" high to fit under lower ADA compliant counters
Built-in capable	Make the best use of space by installing your appliance under the counter
Fully finished black cabinet	Allows the unit to be used freestanding
Stainless steel wrapped door	Durable 304 grade wrapping
Professional horizontal handle	Stainless steel handle mounted horizontally for a modern look
Factory installed lock	Top-mounted for convenient security
Automatic defrost	Reduced maintenance with auto defrost system
Adjustable glass shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup

FF521BLBISSHHADA Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.5"
Width	19.25"
Depth	21.38"
Depth with door at 90°	39.5"
Capacity	4.1 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Energy Usage/Year	406.0kWh/year
Amps	1.4
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs.
Shipping Weight	85.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.75
High Side PSI	205.0
Low Side PSI	103.0
Level Legs Qty	2
Interior Light	Yes
Dimensions	
Interior Height	28.5"
Interior Width	15.75"

Interior Depth	18.0"
Compressor Step Height	8.0"
Compressor Step Width	17.0"
Compressor Step Depth	6.75"

