

# FF521BLDPL



33.5" x 19.25" x 21.38" (H x W x D)

20" wide counter height all-refrigerator for general purpose use, auto defrost with a lock, diamond plate wrapped door and black cabinet

## Highlights:

Slim 20" width is ideal for any setting

Freestanding all-refrigerator offers full 4.1 cu.ft. capacity

Jet black exterior with adjustable glass shelves included

Save time and energy with low maintenance automatic defrost

## Product Features:

Slim 20" width	Full 4.1 cu.ft. capacity inside conveniently slim footprint
Fully finished black cabinet	Allows the unit to be used freestanding
Factory installed lock	Top-mounted for convenient security
Diamond plate door	Unique textured finish offers modern industrial look
Professional towel bar handle	Curved towel bar design in polished stainless steel
Automatic defrost	Reduced maintenance with auto defrost system
Adjustable glass shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup
Crisper drawer	Get the longest life and best taste out of produce by storing greens in a bottom crisper
Flat door liner	Easy to clean, with more depth for storage

## FF521BLDPL Specifications:

Overview	
Height	33.5"
Height to Hinge Cap	34.0"
Width	19.25"
Depth	21.38"
Depth with door at 90°	39.5"
Capacity	4.1 cu.ft.
Defrost Type	Automatic
Door	Diamond Plate
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Energy Usage/Year	406.0kWh/year
Amps	1.4
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs.
Shipping Weight	85.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.75
High Side PSI	205.0
Low Side PSI	103.0
Level Legs Qty	2
Interior Light	Yes
Dimensions	
Interior Height	28.5"
Interior Width	15.75"

Interior Depth	18.0"
Compressor Step Height	8.0"
Compressor Step Width	17.0"
Compressor Step Depth	6.75"

