

FF7BBIDPL



33.25" x 23.63" x 23.5" (H x W x D)

Commercially listed built-in undercounter all-refrigerator for general purpose use, auto defrost w/diamond plate door, TB handle, and black cabinet

Highlights:

Commercially approved for use in foodservice establishments

Flexible design allows built-in or freestanding use in 24" spaces

Automatic defrost saves on user maintenance

Textured diamond plate door in aluminum with polished towel bar handle offers an industrial look

Product Features:

Commercially approved	ETL-S listed to ANSI-NSF Standard 7
Slim undercounter dimensions	Perfectly sized at 24 inches wide for easy placement in any location
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Automatic defrost	Reduced user maintenance with automatic defrost
Fully finished black cabinet	Allows the refrigerator to be used as a freestanding model
Diamond plate wrapped door	Textured aluminum finish for an industrial look
Professional towel bar handle	Curved handle in polished stainless steel completes the look
Adjustable glass shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Interior light on rocker switch	Turn the light on when you need it and off when you're done with a convenient rocker switch

FF7BBIDPL Specifications:

Overview	
Height	33.25"
Height to Hinge Cap	33.75"
Width	23.63"
Depth	23.5"
Depth with Handle	25.75"
Depth with door at 90°	45.5"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Diamond Plate
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	120.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Height Adjustable	1
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"
Interior Depth	17.5"

Compressor Step Height	7.0"
Compressor Step Width	20.0"
Compressor Step Depth	6.0"

