

FF67SSHV



33.5" x 23.63" x 23.5" (H x W x D)

Commercially listed freestanding all-refrigerator for general purpose use, auto defrost w/stainless steel wrapped door, thin handle, and white cabinet

Highlights:

ENERGY STAR certified commercial refrigerator

Commercially approved for use in food service establishments

Stainless steel door complete with sleek handle adds modern elegance to any setting

Full 5.5 cu.ft. capacity inside a convenient 24" footprint

Product Features:

ENERGY STAR certified commercial performance	Meets ENERGY STAR standards as a commercial refrigerator
Commercially approved	ETL-S listed to NSF-7 commercial standards
Slim counter height dimensions	Less than 24 inches wide, with a generous 5.5 c.f. of storage capacity
Fully finished white cabinet	Allows the unit to be used freestanding
Stainless steel wrapped door	Durable design with lasting elegance
Professional stainless steel handle	Thin 14mm diameter on stainless steel handle, mounted vertically for a sleek look
Automatic defrost	Reduced maintenance with auto defrost system
Adjustable shelves	Rearrange the refrigerator space to fit any sized item or remove shelves for simple cleanup
Crisper drawer	Get the longest life and best taste out of produce by storing greens in lower slide drawer

FF67SSHV Specifications:

Overview	
Height	33.5"
Width	23.63"
Depth	23.5"
Depth with Handle	26.38"
Depth with door at 90°	46.13"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	113.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Opaque
Crisper Cover	Glass
Shelf Type	Wire
Shelf Qty	3
Full Door Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"

Interior Width	20.0"
Interior Depth	17.5"
Compressor Step Height	7.0"
Compressor Step Width	20.0"
Compressor Step Depth	6.0"

