

FF7BSSTBADA



32" x 23.63" x 23.5" (H x W x D)

ADA compliant commercial all-refrigerator for freestanding general purpose use, auto defrost w/SS door, towel bar handle, and black cabinet

Highlights:

ENERGY STAR certified commercial refrigerator

Commercially approved for use in foodservice establishments

32" height for use in ADA compliant settings

Stainless steel wrapped door with professional towel bar handle adds luxury to any setting

Product Features:

| | |
|--|--|
| ENERGY STAR certified commercial performance | Meets ENERGY STAR standards as a commercial refrigerator |
| ADA compliant | 32" height for use in settings complying with ADA guidelines for lower counter height |
| Commercially approved | ETL-S listed to NSF-7 Standards for use in commercial establishments |
| Slim counter height dimensions | Less than 24 inches wide with a full 5.5 c.f. capacity |
| Fully finished black cabinet | Allows the refrigerator to be used freestanding |
| Stainless steel door | Durable design with lasting elegance |
| Professional towel bar handle | Curved handle in brushed stainless steel offers a sturdy grip with professional elegance |
| Automatic defrost | Reduced user maintenance with automatic defrost |
| One piece interior liner | Easy clean-up with a seamless liner that won't hold a mess in hidden crevices |

FF7BSSTBADA Specifications:

| Overview | |
|----------------------------|--------------------|
| Height | 32.0" |
| Height to Hinge Cap | 32.25" |
| Width | 23.63" |
| Depth | 23.5" |
| Depth with Handle | 24.25" |
| Depth with door at 90° | 45.0" |
| Capacity | 5.5 cu.ft. |
| Defrost Type | Automatic |
| Door | Stainless Steel |
| Cabinet | Black |
| US Electrical Safety | UL |
| Canadian Electrical Safety | ULC |
| Sanitation | ETL-S |
| Amps | 1.3 |
| Voltage/Frequency | 115 V AC/60 Hz |
| Weight | 100.0 lbs. |
| Shipping Weight | 118.0 lbs. |
| Parts & Labor Warranty | 1 Year |
| Compressor Warranty | 5 Years |
| Refrigerator Features | |
| Door Swing | RHD |
| Reversible | Factory Reversible |
| Shelf Type | Glass |
| Shelf Qty | 3 |
| Adjustable Shelves | Yes |
| Thermostat Type | Dial |
| Refrigerant Type | R134a |
| Refrigerant Amount | 1.8 |
| High Side PSI | 285.0 |
| Low Side PSI | 88.0 |
| Level Legs Qty | 4 |
| Interior Light | Yes |
| Dimensions | |
| Interior Height | 26.25" |
| Interior Width | 21.0" |
| Interior Depth | 17.75" |

| | |
|------------------------|-------|
| Compressor Step Height | 5.5" |
| Compressor Step Width | 21.0" |
| Compressor Step Depth | 5.5" |

