

FF6B7ADA



32" x 23.63" x 23.5" (H x W x D)

ADA compliant commercial all-refrigerator for freestanding general purpose use, with automatic defrost operation and black exterior

Highlights:

ENERGY STAR certified commercial refrigerator

Commercially approved for use in foodservice establishments

32" height for use in ADA compliant settings

Automatic defrost ensures minimum user maintenance

Product Features:

| | |
|--|---|
| ENERGY STAR certified commercial performance | Meets ENERGY STAR standards as a commercial refrigerator |
| Commercially approved | ETL-S listed to NSF-7 commercial standards |
| ADA compliant | 32" height for use in settings complying with ADA guidelines for lower counter height |
| Slim counter height dimensions | Less than 24 inches wide with a full 5.5 c.f. capacity |
| Fully finished black cabinet | Allows the unit to be used freestanding |
| Automatic defrost | Reduced maintenance with auto defrost system |
| Reversible door | User-reversible door swing for added flexibility |
| Hidden evaporator | Cold wall design with hidden evaporator and seamless interior |
| One piece interior liner | Easy clean-up with a seamless liner that won't hold a mess in hidden crevices |

FF6B7ADA Specifications:

| Overview | |
|----------------------------|------------|
| Height | 32.0" |
| Height to Hinge Cap | 32.25" |
| Width | 23.63" |
| Depth | 23.5" |
| Depth with Handle | 25.13" |
| Depth with door at 90° | 46.13" |
| Capacity | 5.5 cu.ft. |
| Defrost Type | Automatic |
| Door | Black |
| Cabinet | Black |
| US Electrical Safety | UL |
| Canadian Electrical Safety | ULC |
| Sanitation | ETL-S |
| Amps | 1.3 |
| Shipping Weight | 102.0 lbs. |
| Parts & Labor Warranty | 1 Year |
| Compressor Warranty | 5 Years |
| Refrigerator Features | |
| Door Swing | RHD |
| Reversible | Yes |
| Crisper Qty | 1 |
| Crisper Finish | Opaque |
| Crisper Cover | Glass |
| Shelf Type | Glass |
| Shelf Qty | 3 |
| Full Door Shelf Qty | 3 |
| Adjustable Shelves | Yes |
| Thermostat Type | Dial |
| Refrigerant Type | R134a |
| Refrigerant Amount | 1.8oz. |
| High Side PSI | 285.0 |
| Low Side PSI | 70.0 |
| Level Legs Qty | 4 |
| Interior Light | Yes |
| Dimensions | |
| Interior Height | 27.75" |
| Interior Width | 20.0" |
| Interior Depth | 17.0" |

| | |
|------------------------|-------|
| Compressor Step Height | 7.0" |
| Compressor Step Width | 20.0" |
| Compressor Step Depth | 6.0" |

