

# FF6BBI7FR



33.25" x 23.63" x 23.5" (H x W x D)

Commercially listed built-in undercounter all-refrigerator for general purpose use, auto defrost w/SS door frame for slide-in panels and black cabinet

## Highlights:

Commercially approved for use in food service establishments

Includes adjustable glass shelves for flexible storage

Flexible design allows built-in or freestanding use in 24" spaces

Stainless steel door frame accepts slide-in panels for a custom look

## Product Features:

Commercially approved	ETL-S listed to NSF-7 commercial standards
Slim undercounter dimensions	Less than 24 inches wide, with a generous 5.5 c.f. of storage capacity
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinetry
Fully finished black cabinet	Allows the unit to be used freestanding
Reversible door	User-reversible door swing for added flexibility
Stainless steel door frame	Slide a panel into this two-piece exposed stainless steel door frame to match the unit to other cabinetry (panel size: 23" W x 28" H at up to 1/4" thick)
Professional stainless steel handle	16 inch long handle can be reversed with door swing
Automatic defrost	Reduced maintenance with auto defrost system
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior

**FF6BBI7FR Specifications:**

Overview	
Height	33.25"
Height to Hinge Cap	34.5"
Width	23.63"
Depth	23.5"
Depth with Handle	25.13"
Depth with door at 90°	45.63"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Panel-Ready
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	107.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Height Adjustable	1
Crisper Qty	1
Crisper Finish	Opaque
Crisper Cover	Glass
Shelf Type	Glass
Shelf Qty	3
Full Door Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes

Dimensions	
Interior Height	27.75"
Interior Width	20.0"
Interior Depth	17.5"
Compressor Step Height	7.0"
Compressor Step Width	20.0"
Compressor Step Depth	6.0"

