

FF6BIADA



32" x 23.63" x 23.5" (H x W x D)

ADA compliant all-refrigerator for built-in general purpose use, with automatic defrost operation and white exterior

Highlights:

32" height for use under lower ADA compliant counters

Flexible design allows built-in or freestanding use

Includes door storage and adjustable shelves

Full 5.5 cu.ft. capacity inside a convenient 24" footprint

Product Features:

ADA compliant	32 inch height fits under standard ADA counters
Slim undercounter dimensions	Less than 24 inches wide with a full 5.5 c.f. capacity
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Fully finished white cabinet	Allows the refrigerator to be used freestanding
Reversible door	User-reversible door swing for added flexibility
Automatic defrost	Reduced maintenance with auto defrost system
Hidden evaporators	Cold wall design with hidden evaporator and seamless interior
One piece interior liner	Easy clean-up with a seamless liner that won't hold a mess in hidden crevices
Adjustable shelves	Rearrange the refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up

FF6BIADA Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Depth with Handle	25.13"
Depth with door at 90°	46.13"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	White
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Shipping Weight	104.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Opaque
Crisper Cover	Glass
Shelf Type	Wire
Shelf Qty	3
Full Door Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"
Interior Depth	17.5"

Compressor Step Height	7.0"
Compressor Step Width	20.0"
Compressor Step Depth	6.0"

