

# FF7LCSSADA



32" x 23.75" x 23.25" (H x W x D)

ADA compliant built-in undercounter all-refrigerator for general purpose or commercial use, auto defrost w/SS wrapped exterior, towel bar handle, and lock

### Highlights:

Commercially approved for use in foodservice establishments

32" height allows installation under lower ADA compliant counters

Complete stainless steel construction adds luxury to any setting

Factory-installed lock provides security you can count on

### Product Features:

Commercially approved	ETL-S listed to NSF-7 Standards for use in commercial establishments
ADA compliant	32 inch height fits under standard ADA counters
Slim undercounter dimensions	Ideal 24" footprint offers full 5.5 cu.ft. storage capacity in a slim fit
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Fully finished cabinet	Allows the refrigerator to be used freestanding
Factory installed lock	Keyed lock for a secure interior
Complete stainless steel construction	Durable design with lasting elegance
Professional towel bar handle	Curved handle in brushed stainless steel offers a sturdy grip with professional elegance
Automatic defrost	Reduced user maintenance with automatic defrost

**FF7LCSSADA Specifications:**

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.75"
Depth	23.25"
Depth with Handle	25.25"
Depth with door at 90°	45.5"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	Stainless Steel
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	143.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Wire
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"
Interior Depth	17.5"

Compressor Step Height	7.0"
Compressor Step Width	20.0"
Compressor Step Depth	6.0"

