

# FF6L7CSSADA



32" x 23.75" x 23.5" (H x W x D)

ADA compliant commercial all-refrigerator for built-in general purpose use, auto defrost with a front lock and fully wrapped SS exterior

## Highlights:

Commercially approved for use in foodservice establishments

32 inch height fits under lower ADA compliant counters

Factory-installed lock provides security you can count on

Complete stainless steel exterior for luxury built to last

## Product Features:

Commercially approved	ETL-S listed to NSF-7 standards for use in commercial settings
ADA compliant	32 inch height fits under standard ADA counters
Complete stainless steel exterior	Stainless steel wrapped cabinet and door for long-lasting durability
Professional towel bar handle	Curved handle in brushed stainless steel
Slim undercounter dimensions	Less than 24 inches wide with a full 5.5 c.f. capacity
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Factory installed lock	Keep contents secure with a key lock on the door
Automatic defrost	Reduced maintenance with auto defrost system
Hidden evaporator	SUMMIT's original "hidden" evaporator is concealed in the wall so it never touches your fingers

**FF6L7CSSADA Specifications:**

<b>Overview</b>	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.75"
Depth	23.5"
Depth with Handle	25.5"
Depth with door at 90°	45.25"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	Stainless Steel
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Shipping Weight	143.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
<b>Refrigerator Features</b>	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Shelf Type	Wire
Shelf Qty	3
Full Door Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
<b>Dimensions</b>	
Interior Height	27.75"

Interior Width	20.0"
Interior Depth	17.5"
Compressor Step Height	7.0"
Compressor Step Width	20.0"
Compressor Step Depth	6.0"

