

# FF6LBIADA



32" x 23.63" x 23.5" (H x W x D)

ADA compliant all-refrigerator for built-in general purpose use, with lock, automatic defrost operation and white exterior

## Highlights:

- 32 inch height fits under lower ADA compliant counters
- Flexible design allows built-in or freestanding use
- Factory-installed lock provides security you can count on
- Automatic defrost ensures minimum user maintenance

## Product Features:

|                              |                                                                                                         |
|------------------------------|---------------------------------------------------------------------------------------------------------|
| ADA compliant                | 32" height to fit under lower ADA compliant counters                                                    |
| Slim undercounter dimensions | Less than 24 inches wide with a full 5.5 c.f. capacity                                                  |
| Built-in capable             | Make the best use of space by installing your appliance under the counter and flush with other cabinets |
| Fully finished white cabinet | Allows the unit to be used freestanding                                                                 |
| Reversible door              | User-reversible door swing for added flexibility                                                        |
| Factory installed lock       | Keyed lock offers added security                                                                        |
| Automatic defrost            | Reduced maintenance with auto defrost system                                                            |
| Hidden evaporator            | Cold wall design with hidden evaporator and seamless interior                                           |
| One piece interior liner     | Easy clean-up with a seamless liner that won't hold a mess in hidden crevices                           |

**FF6LBIADA Specifications:**

| Overview                   |                |
|----------------------------|----------------|
| Height                     | 32.0"          |
| Height to Hinge Cap        | 32.25"         |
| Width                      | 23.63"         |
| Depth                      | 23.5"          |
| Depth with Handle          | 25.13"         |
| Depth with door at 90°     | 46.13"         |
| Capacity                   | 5.5 cu.ft.     |
| Defrost Type               | Automatic      |
| Door                       | White          |
| Cabinet                    | White          |
| US Electrical Safety       | UL             |
| Canadian Electrical Safety | ULC            |
| Amps                       | 1.3            |
| Voltage/Frequency          | 115 V AC/60 Hz |
| Shipping Weight            | 104.0 lbs.     |
| Parts & Labor Warranty     | 1 Year         |
| Compressor Warranty        | 5 Years        |
| Refrigerator Features      |                |
| Door Swing                 | RHD            |
| Reversible                 | Yes            |
| Crisper Qty                | 1              |
| Crisper Finish             | Opaque         |
| Crisper Cover              | Glass          |
| Shelf Type                 | Wire           |
| Shelf Qty                  | 3              |
| Full Door Shelf Qty        | 3              |
| Adjustable Shelves         | Yes            |
| Thermostat Type            | Dial           |
| Fan Type                   | Exterior       |
| Refrigerant Type           | R134a          |
| Refrigerant Amount         | 1.8            |
| High Side PSI              | 285.0          |
| Low Side PSI               | 70.0           |
| Level Legs Qty             | 4              |
| Interior Light             | Yes            |
| Dimensions                 |                |
| Interior Height            | 27.75"         |

|                        |       |
|------------------------|-------|
| Interior Width         | 20.0" |
| Interior Depth         | 17.5" |
| Compressor Step Height | 7.0"  |
| Compressor Step Width  | 20.0" |
| Compressor Step Depth  | 6.0"  |

