



FF71ESTB



46" x 18.75" x 23" (H x W x D)

ENERGY STAR qualified two-door refrigerator-freezer in ADA compliant 46" height with towel bar handles

Highlights:

ENERGY STAR qualified performance ensures annual savings

46" height for select ADA compliant applications

Two-door design for convenience and efficiency in compact size

Towel bar handles allow an easier grip

Product Features:

| | |
|--------------------------------|--|
| ENERGY STAR qualified | Rated by the DOE to perform with more efficiency than federal standards require, saving your unit energy and you on higher utility costs |
| ADA compliant | 46 inch height makes both the refrigerator and freezer accessible under ADA guidelines |
| Professional towel bar handles | Curved handles in brushed stainless steel offer an easier grip for those with arthritis or other joint conditions |
| Thin-line design | Slim width under 19" for an easy fit in space-challenged kitchens |
| Frost-free operation | No-frost convenience for reduced user maintenance |
| Adjustable shelves | Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up |
| Door storage | Store tall bottles and condiments right on the door for convenient access |
| Clear crispener | Get the longest life and best taste out of produce by storing greens in a convenient slide drawer |
| Interior light | Automatically illuminates when you open the door |



FF71ESTB Specifications:

| Overview | |
|----------------------------------|--------------------|
| Height | 46.0" |
| Width | 18.75" |
| Depth | 23.0" |
| Depth with door at 90° | 40.0" |
| Capacity | 4.8 cu.ft. |
| Defrost Type | Frost-Free |
| Door | White |
| Cabinet | White |
| US Electrical Safety | UL |
| Canadian Electrical Safety | ULC |
| Energy Usage/Year | 346.0kWh/year |
| Amps | 0.9 |
| Voltage/Frequency | 115 V AC/60 Hz |
| Weight | 102.0 lbs. |
| Shipping Weight | 130.0 lbs. |
| Parts & Labor Warranty | 1 Year |
| Compressor Warranty | 5 Years |
| Refrigerator-Freezer | |
| Door Swing | RHD |
| Reversible | Factory Reversible |
| Crisper Qty | 1 |
| Crisper Finish | Transparent |
| Crisper Cover | Glass |
| Refrigerator - Interior Height | 24.75" |
| Refrigerator - Interior Width | 16.25" |
| Refrigerator - Interior Depth | 15.75" |
| Refrigerator - Shelf Type | Wire |
| Refrigerator - Shelf Qty | 2 |
| Refrigerator - Full Door Shelves | 3 |
| Freezer - Interior Height | 13.5" |
| Freezer - Interior Width | 13.88" |
| Freezer - Interior Depth | 12.5" |
| Freezer - Shelf Type | Wire |
| Freezer - Shelf Qty | 1 |

| | |
|-----------------------------|----------|
| Freezer - Full Door Shelves | 2 |
| Adjustable Shelves | Yes |
| Interior Light | Yes |
| Thermostat Type | Dial |
| Fan Type | Interior |
| Refrigerant Type | R134a |
| Refrigerant Amount | 2.8 oz. |
| High Side PSI | 260.0 |
| Low Side PSI | 140.0 |
| Level Legs | 2 |
| Compressor Step Height | 6.0" |
| Compressor Step Width | 16.25" |
| Compressor Step Depth | 6.5" |



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799

info@summitappliance.com



www.summitappliance.com