

# FS408BLBI7SSTB



33.5" x 19.25" x 21.38" (H x W x D)

Commercially listed 20" wide built-in undercounter all-freezer, -20° C capable with a lock, stainless steel door, towel bar handle and black cabinet

## Highlights:

ETL-S listed for commercial use

Flexible design allows built-in or freestanding use in 20" wide spaces

-20° C capable with interior slide-out drawers for easy storage

Factory installed lock provides security you can count on

## Product Features:

|   |   |
|---|---|
| Slim 20" width                            | 2.8 capacity inside a slim footprint  |
| Commercially listed                       | ETL-S listed to NSF standards for commercial use                              |
| Built-in capable                          | Make the best use of space by installing your appliance under the counter     |
| Fully finished black cabinet              | Allows the unit to be used freestanding                                       |
| Stainless steel wrapped door              | Durable 304 grade wrapping  |
| Professional towel bar handle             | A curved stainless steel handle provides generous room for a comfortable grip |
| Factory installed lock                    | Top-mounted for convenient security   |
| Hospital grade cord with 'green dot' plug | Secure three-pronged cord for added unit safety                               |
| Manual defrost                            | Efficient performance with reliable temperature stability                     |

**FS408BLBI7SSTB Specifications:**

| Overview                   |                    |
|----------------------------|--------------------|
| Height                     | 33.5"              |
| Height to Hinge Cap        | 34.0"              |
| Width                      | 19.25"             |
| Depth                      | 21.38"             |
| Depth with door at 90°     | 39.5"              |
| Capacity                   | 2.8 cu.ft.         |
| Defrost Type               | Manual             |
| Door                       | Stainless Steel    |
| Cabinet                    | Black              |
| US Electrical Safety       | ETL                |
| Canadian Electrical Safety | ETL-C              |
| Sanitation                 | ETL-S              |
| Energy Usage/Year          | 298.0kWh/year      |
| Amps                       | 1.6                |
| Voltage/Frequency          | 115 V AC/60 Hz     |
| Weight                     | 64.0 lbs.          |
| Shipping Weight            | 85.0 lbs.          |
| Parts & Labor Warranty     | 1 Year             |
| Compressor Warranty        | 5 Years            |
| Freezer                    |                    |
| Door Swing                 | RHD                |
| Reversible                 | Factory Reversible |
| Height Adjustable          | 1                  |
| Interior Height            | 26.38"             |
| Interior Width             | 14.0"              |
| Interior Depth             | 16.75"             |
| Thermostat Type            | Dial               |
| Refrigerant Type           | R134a              |
| Refrigerant Amount         | 3.0 oz.            |
| High Side PSI              | 210.0              |
| Low Side PSI               | 105.0              |
| Level Legs                 | 2                  |
| Interior Drawers           | Yes                |
| Drawers Qty                | 4                  |

