

FF7BBI



33.25" x 23.63" x 23.5" (H x W x D)

Commercially listed built-in undercounter all-refrigerator for general purpose use, with flat door liner, automatic defrost operation and black exterior

Highlights:

ETL-S listed to NSF-7 commercial standards

Flexible design allows built-in or freestanding use in 24" spaces

One piece seamless interior simplifies clean-up

Includes adjustable glass shelves for spill-proof storage

Product Features:

Commercially approved	ETL-S listed to NSF-7 Standards for use in commercial establishments
Automatic defrost	Reduced user maintenance with automatic defrost
Built-in capability	Make the best use of space by installing your refrigerator under the counter and flush with other cabinets
One piece seamless interior liner	Enjoy easy clean-up with a one piece liner that won't hold a mess in hidden crevices
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior
Adjustable glass shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Adjustable thermostat	Dial thermostat for easy temperature management
Interior light on rocker switch	Turn the light on when you need it and off when you're done with a convenient rocker switch located just behind the thermostat
Reversible door	User-reversible door swing

FF7BBI Specifications:

Overview	
Height	33.25"
Height to Hinge Cap	33.75"
Width	23.63"
Depth	23.5"
Depth with Handle	25.13"
Depth with door at 90°	45.63"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Black
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	109.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Height Adjustable	1
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"
Interior Depth	17.5"

Compressor Step Height	7.0"
Compressor Step Width	20.0"
Compressor Step Depth	6.0"

