



SCFF53BXCSSH



34" x 23.63" x 23.5" (H x W x D)

Frost-free built-in undercounter all-freezer for residential or commercial use, with stainless steel wrapped exterior and horizontal handle

Highlights:

True frost-free operation saves you maintenance by preventing icy buildup

Flexible design allows built-in or freestanding use in 24" wide spaces

Full stainless steel wrapped exterior for lasting luxury

Horizontally mounted stainless steel handle brings a modern look under the counter

Product Features:

Frost-free operation	No-frost convenience eliminates the need to manually defrost the unit
Built-in capable	Make the best use of space by installing your freezer under the counter and flush with other cabinets
Stainless steel construction	Exterior cabinet and door are fully wrapped in stainless steel for lasting durability with professional elegance
Professional horizontal handle	Brushed stainless steel handle with a thin 14mm diameter is mounted horizontally across the door for a sleek look
Digital thermostat	Electronic controls offer easy and intuitive temperature management
Recessed LED light	Elegant lighting with an on/off switch located on the control panel
Adjustable shelves	Rearrange your freezer space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Open door alarm	Audible alarm will sound if the door is left open longer than one minute
High temperature alarm	High temperature alarm sounds if the unit's interior goes out of the recommended range



SCFF53BXCSSH Specifications:

Overview	
Height	34.0"
Width	23.63"
Depth	23.5"
Depth with Handle	25.35"
Depth with door at 90°	45.63"
Capacity	4.72 cu.ft.
Defrost Type	Frost-Free
Door	Stainless Steel
Cabinet	Stainless Steel
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Energy Usage/Year	390.0kWh/year
Amps	0.9
Voltage/Frequency	115 V AC/60 Hz
Weight	108.0 lbs.
Shipping Weight	128.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Freezer	
Door Swing	RHD
Reversible	Yes
Interior Height	26.0"
Interior Width	19.0"
Interior Depth	16.0"
Shelf Type	Chrome
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Digital
Interior Light	Yes
Fan Type	Interior and Exterior
Refrigerant Type	R600a
Refrigerant Amount	1.24 oz.
High Side PSI	270.0
Low Side PSI	105.0



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799 info@summitappliance.com  www.summitappliance.com