

# FF7BSSH



33.25" x 23.63" x 23.5" (H x W x D)

Commercially listed freestanding all-refrigerator for general purpose use, auto defrost w/SS wrapped door, horizontal handle, and black cabinet

## Highlights:

ENERGY STAR certified commercial refrigerator

Commercially approved for use in foodservice establishments

Stainless steel door complete with sleek horizontal handle

Automatic defrost minimizes user maintenance

## Product Features:

ENERGY STAR certified commercial performance	Meets ENERGY STAR standards as a commercial refrigerator
Commercially approved	ETL-S listed to NSF-7 Standards for use in commercial establishments
Fully finished black cabinet	Allows the refrigerator to be used freestanding
Stainless steel door	Durable design with lasting elegance
Automatic defrost	Reduced user maintenance with automatic defrost
Professional horizontal handle	Stainless steel handle with sleek 14mm diameter placed horizontally near the top of the door
Adjustable glass shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
One piece interior liner	Enjoy easy clean-up with a seamless liner that won't hold a mess in hidden crevices
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior

## FF7BSSH Specifications:

Overview	
Height	33.25"
Height to Hinge Cap	33.25"
Width	23.63"
Depth	23.5"
Depth with Handle	24.25"
Depth with door at 90°	45.0"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	118.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"
Interior Depth	17.5"
Compressor Step Height	7.0"

Compressor Step Width	20.0"
Compressor Step Depth	6.0"

