

# SCR600LCSSADA



32" x 23.75" x 23.5" (H x W x D)

ADA compliant commercially listed built-in undercounter glass door all-refrigerator with stainless steel cabinet, towel bar handle, and front lock

## Highlights:

Commercially approved for use in food service establishments

32 inch height fits under lower ADA compliant counters

Flexible design allows built-in or freestanding use

Factory installed lock provides security you can count on

## Product Features:

|                                  |  |
|----------------------------------|--|
| ADA Compliant                    | 32 inch height is designed to fit under ADA compliant counters   |
| Commercially approved            | ETL-S listed to NSF-7 Standards for use in commercial establishments                                     |
| Factory installed lock           | Keyed lock for a secure interior   |
| Wrapped stainless steel exterior | Durable elegance built to last   |
| Professional towel bar handle    | A curved handle in brushed stainless steel provides generous room for a comfortable grip                 |
| Built-in capable                 | Make the best use of space by installing your appliance under the counter and flush with other cabinetry |
| Fully finished cabinet           | Allows the unit to be used freestanding  |
| Automatic defrost                | Reduced user maintenance with automatic defrost  |
| Adjustable shelves               | Rearrange the refrigerator space to fit any sized item or remove shelves for simple cleanup              |

**SCR600LCSSADA Specifications:**

| Overview                   |                    |
|----------------------------|--------------------|
| Height                     | 32.0"              |
| Height to Hinge Cap        | 32.25"             |
| Width                      | 23.75"             |
| Depth                      | 23.5"              |
| Depth with Handle          | 26.0"              |
| Depth with door at 90°     | 45.5"              |
| Capacity                   | 5.5 cu.ft.         |
| Defrost Type               | Automatic          |
| Door                       | Glass              |
| Cabinet                    | Stainless Steel    |
| US Electrical Safety       | UL                 |
| Canadian Electrical Safety | ULC                |
| Sanitation                 | ETL-S              |
| Amps                       | 1.3                |
| Voltage/Frequency          | 115 V AC/60 Hz     |
| Weight                     | 120.0 lbs.         |
| Shipping Weight            | 156.0 lbs.         |
| Parts & Labor Warranty     | 1 Year             |
| Compressor Warranty        | 5 Years            |
| Refrigerator Features      |                    |
| Door Swing                 | RHD                |
| Reversible                 | Factory Reversible |
| Shelf Type                 | Wire               |
| Shelf Qty                  | 3                  |
| Adjustable Shelves         | Yes                |
| Thermostat Type            | Dial               |
| Fan Type                   | Exterior           |
| Refrigerant Type           | R134a              |
| Refrigerant Amount         | 1.8                |
| High Side PSI              | 285.0              |
| Low Side PSI               | 88.0               |
| Level Legs Qty             | 4                  |
| Interior Light             | Yes                |
| Dimensions                 |                    |
| Interior Height            | 27.75"             |
| Interior Width             | 20.75"             |
| Interior Depth             | 17.5"              |

|                        |        |
|------------------------|--------|
| Compressor Step Height | 7.0"   |
| Compressor Step Width  | 20.75" |
| Compressor Step Depth  | 5.0"   |

