

# FF7CSSADA



32" x 23.75" x 23.25" (H x W x D)

ADA compliant built-in undercounter all-refrigerator for general purpose or commercial use, auto defrost w/SS wrapped exterior and towel bar handle

### Highlights:

Commercially approved for use in foodservice establishments

32" height allows installation under lower ADA compliant counters

Flexible design allows built-in or freestanding use in 24" spaces

Complete stainless steel exterior for luxury built to last

### Product Features:

ADA compliant	32 inch height fits under standard ADA counters
Commercially approved	ETL-S listed to NSF-7 Standards for use in commercial establishments
Slim undercounter dimensions	Less than 24 inches wide with a full 5.5 c.f. capacity
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Fully wrapped stainless steel cabinet and door	Durable and elegant exterior allows freestanding use
Professional towel bar handle	Curved handle in brushed stainless steel offers a sturdy grip with professional elegance
Automatic defrost	Reduced user maintenance with automatic defrost
One piece interior liner	Easy clean-up with a seamless liner that won't hold a mess in hidden crevices
Adjustable shelves	Rearrange the refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up

**FF7CSSADA Specifications:**

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.75"
Depth	23.25"
Depth with Handle	25.25"
Depth with door at 90°	45.5"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	Stainless Steel
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	143.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Wire
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"
Interior Depth	17.5"

Compressor Step Height	7.0"
Compressor Step Width	20.0"
Compressor Step Depth	6.0"

