

FFAR10



55.13" x 23.63" x 23.5" (H x W x D)

10.1 cu.ft. general purpose auto defrost all-refrigerator with internal fan in thin 24" footprint

Highlights:

24" footprint offers over 10 cu.ft. of storage capacity

Includes full door storage for tall bottles

Automatic defrost minimizes user maintenance

Fan-forced cooling ensures even temperature distribution

Product Features:

Thin-line design	Slim 24" footprint is ideal for space-challenged areas
Full-sized capacity	Over 10 cu.ft. of storage room inside
Automatic defrost	Reduced user maintenance with auto defrost system
Internal fan	Fan-cooled interior for even temperature distribution
Interior light	Automatically illuminates when you open the door
Reversible door	User-reversible door swing allows for more flexibility in placing the unit
Adjustable shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Crisper drawer	Lower slide-out drawer offers convenient storage
Door storage	Keep large bottles and condiments right on the door for easy access

FFAR10 Specifications:

Overview	
Height	55.13"
Height to Hinge Cap	55.5"
Width	23.63"
Depth	23.5"
Depth with Handle	24.75"
Depth with door at 90°	45.5"
Capacity	10.1 cu.ft.
Defrost Type	Automatic
Door	White
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Other Energy Info	120 Volts / 60 Hz.
Amps	1.5
Shipping Weight	155.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Shelf Type	Wire
Shelf Qty	4
Full Door Shelf Qty	5
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Interior
Refrigerant Type	R134a
Refrigerant Amount	3.0
High Side PSI	290.0
Low Side PSI	70.0
Level Legs Qty	2
Interior Light	Yes
Dimensions	
Interior Height	48.25"

Interior Width	20.5"
Interior Depth	17.75"
Compressor Step Height	6.25"
Compressor Step Width	20.0"
Compressor Step Depth	5.5"

