

FS407LBI7FR



33.5" x 19.25" x 21.38" (H x W x D)

Commercially listed 20" wide built-in undercounter all-freezer, -20° C capable with a lock and stainless steel door frame for slide-in custom panels

Highlights:

Flexible design allows built-in or freestanding use in 20" wide spaces

ETL-S listed for commercial use

Factory installed lock provides security you can count on

Slide your own panel into the door frame for an easy custom look

Product Features:

Commercially listed	ETL-S listed to NSF standards for commercial use
Slim 20" width	2.8 capacity inside a slim footprint
Built-in capable	Make the best use of space by installing your appliance under the counter
Fully finished white cabinet	Allows the unit to be used freestanding
Factory installed lock	Top-mounted for convenient security
Stainless steel door frame	Two-piece "U"-shaped door frame accepts slide-in custom panels (panel size: 19 1/4" W x 31 1/4" H at up to 1/4" thick)
Reversible door	Keep your options flexible with a reversible door that is easy to switch when your arrangement changes
Hospital grade cord with 'green dot' plug	Secure three-pronged cord for added unit safety
Manual defrost	Efficient performance with reliable temperature stability

FS407LBI7FR Specifications:

Overview	
Height	33.5"
Height to Hinge Cap	34.0"
Width	19.25"
Depth	21.38"
Depth with door at 90°	39.5"
Capacity	2.8 cu.ft.
Defrost Type	Manual
Door	Panel-Ready
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Energy Usage/Year	298.0kWh/year
Amps	1.6
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs.
Shipping Weight	85.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Freezer	
Door Swing	RHD
Reversible	Yes
Height Adjustable	1
Interior Height	26.38"
Interior Width	14.0"
Interior Depth	16.75"
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	3.0 oz.
High Side PSI	210.0
Low Side PSI	105.0
Level Legs	2
Interior Drawers	Yes
Drawers Qty	4

