

FS408BLBIADA



32" x 19.25" x 21.38" (H x W x D)

ADA Compliant 20" wide built-in undercounter all-freezer for general purpose use, -20° C capable with a lock and black finish

Highlights:

32" height fits under lower ADA compliant counters

Flexible design allows built-in or freestanding use in 20" wide spaces

Factory installed lock provides security you can count on

-20° C capable with interior slide-out drawers for easy storage

Product Features:

ADA compliant	32" high to fit under lower ADA compliant counters
Slim 20" width	2.8 capacity inside a slim footprint
Built-in capable	Make the best use of space by installing your appliance under the counter
Fully finished black cabinet	Allows the unit to be used freestanding
Factory installed lock	Top-mounted for convenient security
Reversible door	Keep your options flexible with a reversible door that is easy to switch when your arrangement changes
Manual defrost	Efficient performance with reliable temperature stability
-20° capable	Low temperature capability ideal for certain sensitive items
Pull-out drawers	Four clear baskets for convenient and separated storage

FS408BLBIADA Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.5"
Width	19.25"
Depth	21.38"
Depth with Handle	23.0"
Depth with door at 90°	39.5"
Capacity	2.8 cu.ft.
Defrost Type	Manual
Door	Black
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Energy Usage/Year	298.0kWh/year
Amps	1.6
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs.
Shipping Weight	80.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Freezer	
Door Swing	RHD
Reversible	Yes
Interior Height	26.38"
Interior Width	14.0"
Interior Depth	16.75"
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	3.0 oz.
High Side PSI	210.0
Low Side PSI	105.0
Level Legs	2
Interior Drawers	Yes
Drawers Qty	4

