

# R17FF



67.5" x 34" x 28.25" (H x W x D)

Large capacity all-refrigerator with frost-free operation and fan-forced cooling

## Highlights:

True frost-free operation saves you maintenance by preventing icy buildup

Fully featured for convenient storage with adjustable shelves and door racks

Nearly 17 c.f. of storage capacity

Right hand door swing

## Product Features:

Frost-free operation	No-frost convenience requires no manual defrosting
Adjustable shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Door storage	Keep large bottles and condiments right on the door for easy access
Adjustable thermostat	Manage the interior temperature with ease and accuracy
Interior light	Automatically illuminates when you open the door
100% CFC free	Environmentally friendly design without ozone-damaging chemicals

## R17FF Specifications:

Overview	
Height	67.5"
Width	34.0"
Depth	28.25"
Capacity	16.5 cu.ft.
Defrost Type	Frost-Free
Door	White
Cabinet	White
US Electrical Safety	UL
Energy Usage/Year	318.0kWh/year
Amps	5.0
Voltage/Frequency	115 V AC/60 Hz
Weight	230.0 lbs.
Shipping Weight	245.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	No
Shelf Type	Wire
Shelf Qty	4
Full Door Shelf Qty	4
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Interior
Refrigerant Type	R134a
Refrigerant Amount	3.5oz.
High Side PSI	320.0
Low Side PSI	140.0
Interior Light	Yes

