

SCR1300CSS



73" x 23.63" x 23.5" (H x W x D)

Commercial full-sized beverage merchandiser with automatic defrost in slim width and stainless steel cabinet

Highlights:

Full fluorescent light offers ideal display of stored products

Tropicalized glass door design keeps products well-preserved

Ideal 24" footprint offers large capacity with storage all the way to the floor

Stainless steel cabinet adds professional look


Product Features:

Commercial design	Meets UL-Commercial Standard 471
Thin-line design	Convenient 24" footprint fits easily in many tight locations
Double pane tempered glass door	Tropicalized design protects contents from ambient hot temperatures
Stainless steel cabinet	304 grade stainless steel for an attractive and durable finish
Automatic defrost	Reduced maintenance with auto defrost system
Adjustable shelves	Slide-out shelving with no clips for faster adjusting
Factory reversible door	Unit ships RHD. Door swing can be specified upon order or reversed in the field with an optional left-hand hinge
Fluorescent lighting	Fully illuminates the interior on a convenient ON/OFF switch
Internal fan	Even circulation throughout the interior



SCR1300CSS Specifications:

Overview	
Height	73.0"
Width	23.63"
Depth	23.5"
Capacity	13.0 cu.ft.
Defrost Type	Automatic
Door	Glass
Cabinet	Stainless Steel
US Electrical Safety	ETL
Amps	5.4
Voltage/Frequency	115 V AC/60 Hz
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Wire
Shelf Qty	4
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Interior
Refrigerant Type	R134a
Refrigerant Amount	5.2
High Side PSI	430.0
Low Side PSI	87.0
Interior Light	Yes
Dimensions	
Interior Height	62.5"
Interior Width	19.25"
Interior Depth	17.25"
Compressor Step Height	8.0"
Compressor Step Width	19.25"
Compressor Step Depth	6.0"



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799

info@summitappliance.com



www.summitappliance.com

