

SCR500BLBI7HHADA



32" x 19.94" x 22.25" (H x W x D)

Commercially listed ADA Compliant 20" wide glass door all-refrigerator for built-in use, auto defrost with a lock, horizontal handle and black cabinet

Highlights:

ETL-S listed for commercial use

32" height fits under lower ADA compliant counters

Flexible design allows built-in or freestanding use in 20" wide spaces

Glass door offers full display of interior

Product Features:

Commercially listed	ETL-S listed to NSF standards for commercial use
ADA compliant	32" high to fit under lower ADA compliant counters
Slim 20" width	Full 4.1 cu.ft. capacity inside conveniently slim footprint
Built-in capable	Make the best use of space by installing your appliance under the counter
Glass door	Heat resistant design offers full view of interior
Fully finished black cabinet	Allows the unit to be used freestanding
Factory installed lock	Keyed lock for secure interior
Professional horizontal handle	Thin 14mm diameter on stainless steel handle, mounted horizontally on the door
Reversible door	Keep your options flexible with a reversible door that is easy to switch when your arrangement changes



SCR500BLBI7HHADA Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.56"
Width	19.94"
Depth	22.25"
Capacity	4.1 cu.ft.
Defrost Type	Automatic
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Amps	1.4
Voltage/Frequency	115 V AC/60 Hz
Weight	60.0 lbs.
Shipping Weight	83.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.75
High Side PSI	205.0
Low Side PSI	103.0
Level Legs Qty	2
Wheel Qty	2
Interior Light	Yes
Dimensions	
Interior Height	29.0"
Interior Width	17.0"
Interior Depth	17.0"



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799

info@summitappliance.com

www.summitappliance.com