

# SCR600LSH



33.5" x 23.63" x 23.5" (H x W x D)

Commercially listed freestanding glass door all-refrigerator with white cabinet, lock, and full-length stainless steel handle

## Highlights:

Commercially approved for use in foodservice establishments

Glass door provides attractive view of stored products

Factory-installed lock offers security you can count on

SUMMIT's "hidden" evaporator maximizes space and simplifies cleanup

## Product Features:

Commercially approved	ETL-S listed to NSF-7 Standards for use in commercial establishments
Fully finished white cabinet	Allows the unit to be used freestanding
Double pane tempered glass door	Heat resistant design provides clear view to promote impulse buys
Factory installed lock	Keyed lock for a secure interior
Full-length towel bar handle	Professional stainless steel handle with curved design covers the full length of the door
Automatic defrost	Reduced user maintenance with automatic defrost
Adjustable shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
One piece interior liner	Enjoy easy clean-up with a seamless liner that won't hold a mess in hidden crevices
Interior light on rocker switch	Turn the light on when you need it and off when you're done with a convenient rocker switch

**SCR600LSH Specifications:**

<b>Overview</b>	
Height	33.5"
Width	23.63"
Depth	23.5"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Glass
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Weight	120.0 lbs.
Shipping Weight	125.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
<b>Refrigerator Features</b>	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Wire
Shelf Qty	4
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	2
Interior Light	Yes
<b>Dimensions</b>	
Interior Height	26.0"
Interior Width	20.75"
Interior Depth	17.5"
Compressor Step Height	6.0"
Compressor Step Width	20.75"
Compressor Step Depth	5.0"

