

SCUR18



73.25" x 34" x 25.5" (H x W x D)

Commercially approved frost-free all-refrigerator with digital thermostat, casters, right hand door swing, and lock

Highlights:

Commercially approved for use in foodservice establishments

Digital thermostat with external readout for easy and accurate temperature control

Sturdy handle in durable stainless steel

True frost-free operation saves you maintenance by preventing icy buildup

Product Features:

Commercially approved	UL-S listed to NSF-7 for commercial use
Large capacity	Nearly 17 c.f. of storage space inside
Frost-free operation	No-frost convenience requires no manual defrosting
Digital thermostat	Precise temperature management and external readout with easy electronic controls
6 inch casters	Heavy duty wheels for added mobility
Door storage	Store large bottles right on the door for easy access
Adjustable shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Professional towel bar handle	A curved stainless steel handle provides generous room for a comfortable grip
Basket	More storage options with a slide-out basket at the bottom

SCUR18 Specifications:

Overview	
Height	73.25"
Width	34.0"
Depth	25.5"
Depth with Handle	30.75"
Capacity	16.7 cu.ft.
Defrost Type	Frost-Free
Door	White
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	UL-S
Amps	5.0
Voltage/Frequency	115 V AC/60 Hz
Weight	245.0 lbs.
Shipping Weight	325.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	No
Shelf Type	Wire
Shelf Qty	3
Full Door Shelf Qty	5
Adjustable Shelves	Yes
Thermostat Type	Digital
Fan Type	Interior
Wheel Qty	4
Interior Light	Yes

