

HP-15A, 15-TON HYDRAULIC PRESS

331416

JET's Hydraulic Shop Press line consists of a 5, 15 and 35 ton hydraulically powered H frame press. Each machine is built using heavy steel plate that is electro welded together, and comes standard with industrial grade hydraulics. These machines are for the serious fabrication and machine shop owner who demands only the best quality from his operation.



FEATURES

- *HP-15A Shown in Image
- For pressing, bending and straightening operations
- Easy-to-use, hand-operated with pressure gauge for direct pressure readings
- Tables raise and lower easily with use of hand crank on the 15- and 35- ton models
- Side frames are open for inserting long material
- Fast setup ram extension screw
- Ram moves laterally for added versatility (15- and 35-ton models)
- Two bed plates and pump handles
- Straightness testing support uses centers or v-blocks on the 15 and 35 Ton models



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

HP-15A, 15-TON HYDRAULIC PRESS

331416

SPECIFICATIONS

Capacity (Tons)	15
Ram Diameter (In.)	2-1/2
Piston Stroke (In.)	4-1/2
Screw Stroke (In.)	3-1/8
Work Table Size (In.)	24-3/4 x 7-1/2
Lateral Movement (In.)	10-3/16
Vertical Table Travel (In.)	22-3/16
Overall Dimensions (L x W xH) (In.)	34 x 30 x 66
Weight (Lbs.)	435



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE