

# J-A3008M-PF2, 25" ARBOGA GEAR HEAD DRILL PRESS WITH POWER DOWN FEED 220V, 3PH

354036

This premier drill combines power and precision with a speed range of 108-1800 RPMs to handle virtually any drilling application. Driven by a sturdy 3HP motor, the drilling capabilities of up to 1-7/8" and tapping to 1" in steel! Exceptional support is provided by a large 5-1/2" steel column. Power down feed engagement is controlled by one selector switch which makes this the perfect drill press for any shop.



## FEATURES

- Fiber and steel gears, which do not require an oil bath, allow for easier speed changes
- No-volt release, prevents spindle start up when power returns after shut down
- Adjustable taper bearings mounted in the end of the quill
- Head and table rotates 360° around column
- Drill head and table can be raised and lowered
- Helical gears for smooth, quiet operation
- Quick release drill ejector
- English/metric depth gauge
- Machined, T-slotted base plate
- Steel column
- Extra long quill movement
- Fully enclosed spindle
- Large T-slotted table
- Telescoping safety spindle guard



## JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

# J-A3008M-PF2, 25" ARBOGA GEAR HEAD DRILL PRESS WITH POWER DOWN FEED 220V, 3PH

354036

## SPECIFICATIONS

Style (Type)	Geared Head
Drills to Center of Circle (In.)	25
Drilling Capacity Cast Iron (In.)	1-3/16
Drilling Capacity Mild Steel (In.)	31/32
Column Diameter (In.)	4-1/2
Distance Column to Spindle (In.)	12-5/8
Range of Spindle Speeds (RPM)	90, 190, 320, 530, 640, 1060, 1790, 3610
Spindle Taper (In. x TPI)	MT-3
Spindle Travel (In.)	6
Spindle Distance to Base (In.)	45-5/8
Spindle Distance to Table (Max.) (In.)	35
Table Size (L x W) (In.)	15-3/4 x 19-3/4
Table Travel (In.)	30
T-Slots Number and Size (In.)	2 - 9/16
Work Table Weight Capacity (Lbs.)	450
Base Dimensions (In.)	28 x 24
Base Slots Number & Size (In.)	2 & 9/16



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE