

J-CK350-4K, 350MM NON-FERROUS HIGH SPEED MANUAL COLD SAW

414207K

JET Coldsaws deliver clean, burr-free cuts and offer machine shop and fabrication professionals a list of features and standard design characteristics that you've come to expect from JET. All backed by the industry leading full service Two Year Warranty



FEATURES

- 350mm (14") Non-Ferrous High Speed Cold Saw
- Spring loaded whole hand trigger starts or stops the sawing process for easy smooth cutting and increased user safety
- Quick tension and release mitering capabilities with stops at 45° right, 45° left, and 90° (center), capable of slotting
- Two-piece blade guard system permits quick and easy blade changes without removing the guards
- Heavy-Duty cast iron frame base with easy access storage provides a stable cutting platform
- Double self centering vise with adjustable gibs secures the material for burr free cuts
- Flood style coolant with flow control system extends blade life
- 30" adjustable length material stop
- High-Speed NF-350mm Blade included
- High-Speed NF-350mm Blade



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

J-CK350-4K, 350MM NON-FERROUS HIGH SPEED MANUAL COLD SAW

414207K

SPECIFICATIONS

Style (Type)	Non-Ferrous
Blade Speeds (RPM)	1750, 3500
Tubing Round at 90 Degrees (In.)	4-1/2
Tubing Round at 45 Degrees (In.)	3-1/2
Tubing Square at 90 Degrees (In.)	4-3/16 x 4-3/16
Tubing Square at 45 Degrees (In.)	3-1/2 x 3-1/2
Tubing Rectangle at 90 Degrees (In.)	5-1/2 x 3-57/64
Tubing Rectangle at 45 Degrees (In.)	3-19/64 x 3
Solid Round at 90 Degrees (In.)	2
Solid Round at 45 Degrees (In.)	1-11/16
Solid Square at 90 Degrees (In.)	2 x 2
Solid Square at 45 Degrees (In.)	1-11/16 x 1-11/16
Blade Size (Mm.)	350 x 32 x 3-2/5
Maximum Vise Opening (In.)	6
Motor (HP)	2 HP, 440V, 3Ph
Overall Dimensions (L x W xH) (In.)	25 x 52 x 73
Weight (Lbs.)	683



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

J-CK350-4K, 350MM NON-FERROUS HIGH SPEED MANUAL COLD SAW

414207K

FULL SERIES

STOCK NO	MODEL NO	STYLE (TYPE)	BLADE SPEEDS (RPM)	CUTTING CAPACITY TUBING (IN.)	TUBING ROUND AT 90 DEGREES (IN.)	TUBING ROUND AT 45 DEGREES (IN.)
414203K	J-CK350-2K	Non-Ferrous	1750, 3500		4-1/2	3-1/2
414207K	J-CK350-4K	Non-Ferrous	1750, 3500		4-1/2	3-1/2

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE