

**1. PRODUCT AND COMPANY IDENTIFICATION****Product identifier****Product Name** Multi-Purpose Cleaner Degreaser**Other means of identification****Product Code** 640407 - 670175**Synonyms** None**Details of the supplier of the safety data sheet****Company Name** Global Industrial  
2505 Mill Center Parkway  
Buford GA 30518  
(516) 608-3000**Emergency telephone number****Emergency Telephone** Chemtrec (US & Canada) 800-424-9300  
Chemtrec (outside US & Canada) 703-527-3887**2. HAZARDS IDENTIFICATION****Classification****OSHA Regulatory Status**

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Not classified
Acute toxicity - Dermal	Not classified
Skin corrosion/irritation	Category 3

**Label elements****Emergency Overview****Warning****Hazard statements**

Causes mild skin irritation

**Appearance** Clear**Physical state** Liquid**Odor** Sassafras**Precautionary Statements - Prevention**Use only in a well-ventilated area  
Wear protective gloves/protective clothing/eye protection/face protection  
Do not breathe dust/fume/gas/mist/vapors/spray  
Do not eat, drink or smoke when using this product  
Wash face, hands and any exposed skin thoroughly after handling**Precautionary Statements - Response**Specific Treatment (See Section 4 on the SDS)  
If skin irritation occurs: Get medical advice/attention  
IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing  
Call a POISON CENTER or doctor/physician if you feel unwell  
IF SWALLOWED: Rinse mouth. DO NOT induce vomiting

Drink plenty of water  
Immediately call a POISON CENTER or doctor/physician

**Precautionary Statements - Disposal**

Disposal should be in accordance with applicable regional, national and local laws and regulations

**Hazards not otherwise classified (HNOC)****Other Information**

- Harmful to aquatic life with long lasting effects
- Harmful to aquatic life

Unknown Acute Toxicity 0.02% of the mixture consists of ingredient(s) of unknown toxicity

### 3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
Surfactant Blend	Proprietary	1-5	*
1-Butoxy-2-Propanol	5131-66-8	1-5	*

\*The exact percentage (concentration) of composition has been withheld as a trade secret.

### 4. FIRST AID MEASURES

**First aid measures**

<b>Skin Contact</b>	Wash off immediately with plenty of water. Wash skin with soap and water.
<b>Eye contact</b>	Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.
<b>Inhalation</b>	Remove to fresh air.
<b>Ingestion</b>	Clean mouth with water and drink afterwards plenty of water.

**Most important symptoms and effects, both acute and delayed**

**Symptoms** Any additional important symptoms and effects are described in Section 11: Toxicology Information.

**Indication of any immediate medical attention and special treatment needed**

**Note to physicians** Treat symptomatically.

### 5. FIRE-FIGHTING MEASURES

**Suitable extinguishing media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Unsuitable extinguishing media** Caution: Use of water spray when fighting fire may be inefficient.

**Specific hazards arising from the chemical**

No Information available.

**Explosion data**

**Sensitivity to Mechanical Impact** None.

**Sensitivity to Static Discharge** None.

**Protective equipment and precautions for firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

### 6. ACCIDENTAL RELEASE MEASURES

**Personal precautions, protective equipment and emergency procedures**

**Personal precautions** Ensure adequate ventilation, especially in confined areas.

**Environmental precautions**

**Environmental precautions** Do not allow into any storm sewer drains, lakes, streams, ponds, estuaries, oceans or other surface water bodies. Should not be released into the environment. Dispose of according to all local city, state and federal rules and regulations.

**Methods and material for containment and cleaning up**

**Methods for containment** Prevent further leakage or spillage if safe to do so.

**Methods for cleaning up** Pick up and transfer to properly labeled containers.

**7. HANDLING AND STORAGE****Precautions for safe handling**

**Advice on safe handling** Handle in accordance with good industrial hygiene and safety practice.

**Conditions for safe storage, including any incompatibilities**

**Storage Conditions** Keep containers tightly closed in a dry, cool and well-ventilated place.

**Incompatible materials** None known based on information supplied.

**8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control parameters****Exposure Guidelines**

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
2-(2-methoxypropoxy)propano 34590-94-8	STEL: 150 ppm TWA: 100 ppm S*	TWA: 100 ppm TWA: 600 mg/m <sup>3</sup> (vacated) TWA: 100 ppm (vacated) TWA: 600 mg/m <sup>3</sup> (vacated) STEL: 150 ppm (vacated) STEL: 900 mg/m <sup>3</sup> (vacated) S* S*	IDLH: 600 ppm TWA: 100 ppm TWA: 600 mg/m <sup>3</sup> STEL: 150 ppm STEL: 900 mg/m <sup>3</sup>
Sodium Hydroxide 1310-73-2	Ceiling: 2 mg/m <sup>3</sup>	TWA: 2 mg/m <sup>3</sup> (vacated) Ceiling: 2 mg/m <sup>3</sup>	IDLH: 10 mg/m <sup>3</sup> Ceiling: 2 mg/m <sup>3</sup>

*NIOSH IDLH Immediately Dangerous to Life or Health*

**Other Information** Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

**Appropriate engineering controls**

**Engineering Controls** Showers, Eyewash stations & Ventilation systems.

**Individual protection measures, such as personal protective equipment**

**Eye/face protection** Wear safety glasses with side shields (or goggles).

**Skin and body protection** Wear protective gloves and protective clothing.

**Respiratory protection** If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

**General Hygiene** Handle in accordance with good industrial hygiene and safety practice.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

### Information on basic physical and chemical properties

<b>Physical state</b>	Liquid
<b>Appearance</b>	Clear
<b>Color</b>	Green
<b>Odor</b>	Sassafras
<b>Odor threshold</b>	No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	9.0 - 10.5	
Specific Gravity	1.01	
Viscosity	<25 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	None	
Boiling point / boiling range	100 °C / 212 ° F Degrees	
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	
Flammability Limits in Air		
Upper flammability limit:	No Information available	
Lower flammability limit:	No Information available	
Vapor pressure	No Information available	
Vapor density	No Information available	
Water solubility	Complete	
Partition coefficient	No Information available	
Autoignition temperature	No Information available	
Decomposition temperature	No Information available	

### Other Information

Density Lbs/Gal	8.41
VOC Content (%)	3.5

## 10. STABILITY AND REACTIVITY

### Reactivity

No data available

### Chemical stability

Stable under recommended storage conditions.

### Possibility of Hazardous Reactions

None under normal processing.

### Conditions to avoid

Extremes of temperature and direct sunlight.

### Incompatible materials

None known based on information supplied.

### Hazardous Decomposition Products

None known based on information supplied.

## 11. TOXICOLOGICAL INFORMATION

### Information on likely routes of exposure

#### Product Information

<b>Inhalation</b>	Avoid breathing vapors or mists. May cause irritation of respiratory tract.
-------------------	---

<b>Eye contact</b>	Avoid contact with eyes. Direct contact may cause redness and irritation.
<b>Skin Contact</b>	Avoid contact with skin. Prolonged or repeated contact may dry skin and cause irritation.
<b>Ingestion</b>	Do not taste or swallow. May cause gastro intestinal irritation.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Surfactant Blend	> 2000 mg/kg ( Rat )	> 2000 mg/kg ( Rat )	-
1-Butoxy-2-Propanol 5131-66-8	= 5660 µL/kg ( Rat ) = 1900 mg/kg ( Rat )	= 3100 mg/kg ( Rabbit )	-

**Information on toxicological effects**

**Symptoms** No Information available.

**Delayed and immediate effects as well as chronic effects from short and long-term exposure**

<b>Irritation</b>	MAY CAUSE SKIN IRRITATION.
<b>Sensitization</b>	No Information available.
<b>Germ cell mutagenicity</b>	No Information available.
<b>Carcinogenicity</b>	No Information available.
<b>Reproductive toxicity</b>	No Information available.
<b>STOT - single exposure</b>	No Information available.
<b>STOT - repeated exposure</b>	No Information available.
<b>Target organ effects</b>	Central nervous system, EYES, Respiratory system.
<b>Aspiration hazard</b>	No Information available.

**Numerical measures of toxicity - Product Information**

**Unknown Acute Toxicity** 0.02% of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document .

<b>ATEmix (oral)</b>	62,848.00
<b>ATEmix (dermal)</b>	50,032.00

**12. ECOLOGICAL INFORMATION****Ecotoxicity**

1.77% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
Surfactant Blend	-	1.2: 96 h Oncorhynchus mykiss mg/L LC50	5.3: 48 h Daphnia mg/L LC50
2-(2-methoxypropoxy)propano 34590-94-8	-	10000: 96 h Pimephales promelas mg/L LC50 static	1919: 48 h Daphnia magna mg/L LC50
Tetrasodium EDTA 64-02-8	1.01: 72 h Desmodesmus subspicatus mg/L EC50	59.8: 96 h Pimephales promelas mg/L LC50 static 41: 96 h Lepomis macrochirus mg/L LC50 static	610: 24 h Daphnia magna mg/L EC50
Trisodium nitrilotriacetate 5064-31-3	560 - 1000: 96 h Chlorella vulgaris mg/L EC50	93 - 170: 96 h Pimephales promelas mg/L LC50 flow-through 252: 96 h Lepomis macrochirus mg/L LC50 560 - 1000: 96 h Oryzias latipes mg/L LC50 semi-static 72 - 133: 96 h Oncorhynchus mykiss mg/L LC50 static 560 - 1000: 96 h Poecilia reticulata mg/L LC50 560 - 1000: 96 h Poecilia reticulata mg/L LC50 semi-static 470: 96 h Pimephales promelas mg/L LC50 static 175 - 225: 96 h Lepomis macrochirus mg/L LC50 static 560 - 1000: 96 h Oryzias latipes mg/L LC50 114: 96 h Pimephales promelas mg/L LC50	560 - 1000: 48 h Daphnia magna mg/L LC50
Sodium Hydroxide	-	45.4: 96 h Oncorhynchus mykiss	-

1310-73-2		mg/L LC50 static	
-----------	--	------------------	--

**Persistence and degradability**

No Information available.

**Bioaccumulation**

Bioaccumulative potential.

**Other adverse effects**

No Information available

### 13. DISPOSAL CONSIDERATIONS

**Waste treatment methods****Disposal of wastes**

Disposal should be in accordance with applicable regional, national and local laws and regulations.

**Contaminated packaging**

Do not reuse container.

This product contains one or more substances that are listed with the State of California as a hazardous waste.

### 14. TRANSPORT INFORMATION

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

**DOT**

Not regulated

**TDG**

Not regulated

### 15. REGULATORY INFORMATION

**International Inventories****TSCA**

Complies

**DSL/NDSL**

Complies

**Legend:****TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List**US Federal Regulations****SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	SARA 313 - Threshold Values %
2-(2-methoxypropoxy)propano - 34590-94-8	1.0

**SARA 311/312 Hazard Categories**

<b>Acute health hazard</b>	No
<b>Chronic Health Hazard</b>	No
<b>Fire hazard</b>	No
<b>Sudden release of pressure hazard</b>	No
<b>Reactive Hazard</b>	No

**CWA (Clean Water Act)**

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

**CERCLA**

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

### US State Regulations

#### California Proposition 65

This product has been evaluated and does not require warning labeling under California Proposition 65.

### U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
2-(2-methoxypropoxy)propano 34590-94-8	X	X	X
Trisodium nitrilotriacetate 5064-31-3	-	X	-
Sodium Hydroxide 1310-73-2	X	X	X

### U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

## 16. OTHER INFORMATION

<u>NFPA</u>	Health hazards 0	Flammability 0	Instability 0	Physical and Chemical Properties -
<u>HMIS</u>	Health hazards 0	Flammability 0	Physical hazards 0	Personal protection B

Issue Date 08-Mar-2018

Revision Date 07-Mar-2018

#### Revision Note

No Information available

#### Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

**End of Safety Data Sheet**