

Safety Data Sheet

Restor-A-Finish

SDS Revision Date:

08/20/2014

1. Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product Identity / Alternate Names

Restor-A-Finish

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use / Application Method

See Technical Data Sheet.

1.3. Details of the supplier of the safety data sheet

Company Name

Howard Products, Inc.
560 Linne Road
Paso Robles, CA 93446

Emergency

CHEMTREC (USA)

(800) 424-9300

Customer Service: Howard Products, Inc.

EMERGENCY PHONE: 1-805-227-1000
FAX PHONE: 1-805-227-1007

2. Hazard identification of the product

2.1. Classification of the substance or mixture

Flam. Liq. 2;H225

Highly Flammable liquid and vapor.

Acute Tox. 4;H332

Harmful if inhaled.

Skin Irrit. 3;H316

Causes mild skin irritation. (Not adopted by US OSHA)

Eye Irrit. 2;H319

Causes serious eye irritation.

2.2. Label elements

Using the Toxicity Data listed in section 11 and 12 the product is labeled as follows.



Danger

H225 Highly flammable liquid and vapor.

H316 Causes mild skin irritation.

H319 Causes serious eye irritation.

H332 Harmful if inhaled.

Safety Data Sheet

Restor-A-Finish

SDS Revision Date:

08/20/2014

[Prevention]:

P210 Keep away from heat / sparks / open flames / hot surfaces - No smoking.

P241 Use explosion-proof electrical / ventilating / light / equipment.

P261 Avoid breathing dust / fume / gas / mist / vapors / spray.

P264 Wash thoroughly after handling.

P271 Use only outdoors or in a well-ventilated area.

P280 Wear protective gloves / eye protection / face protection.

[Response]:

P303+361+353 IF ON SKIN (or hair): Remove / Take off immediately all contaminated clothing. Rinse skin with water / shower.

P304+312 IF INHALED: Call a POISON CENTER or doctor / physician if you feel unwell.

P305+351+338 IF IN EYES: Rinse continuously with water for several minutes. Remove contact lenses if present and easy to do - continue rinsing.

P332+313 If skin irritation occurs: Get medical advice / attention.

P337+313 If eye irritation persists: Get medical advice / attention.

P340 Remove victim to fresh air and keep at rest in a position comfortable for breathing.

P370+378 In case of fire: Use extinguishing media listed in section 5 of SDS for extinction.

[Storage]:

P403+233 Store in a well ventilated place. Keep container tightly closed.

[Disposal]:

P501 Dispose of contents / container in accordance with local / national regulations.

3. Composition/information on ingredients

This product contains the following substances that present a hazard within the meaning of the relevant State and Federal Hazardous Substances regulations.

Ingredient/Chemical Designations	Weight %	GHS Classification	Notes
Distillates (petroleum), hydrotreated heavy paraffinic CAS Number: 0064742-54-7	50 - 75	Carc. 1A;H350	[1]
Petroleum distillates, hydrotreated light CAS Number: 0064742-47-8	25 - 50	Asp. Tox. 1;H304	[1]
Isopropyl Alcohol CAS Number: 0000067-63-0	1.0 - 10	Flam. Liq. 2;H225 Eye Irrit. 2;H319 STOT SE 3;H336	[1][2]
Acetone CAS Number: 0000067-64-1	1.0 - 10	Flam. Liq. 2;H225 Eye Irrit. 2;H319 STOT SE 3;H336	[1][2]
Butanone CAS Number: 0000078-93-3	1.0 - 10	Flam. Liq. 2;H225 Eye Irrit. 2;H319 STOT SE 3;H336	[1][2]
Xylene CAS Number: 0001330-20-7	1.0 - 10	Flam. Liq. 3;H226 Acute Tox. 4;H332 Acute Tox. 4;H312 Skin Irrit. 2;H315	[1][2]
Gilsonite CAS Number: 0012002-43-6	1.0 - 10		[1]

[1] Substance classified with a health or environmental hazard.

[2] Substance with a workplace exposure limit.

[3] PBT-substance or vPvB-substance.

*The full texts of the phrases are shown in Section 16.

Safety Data Sheet

Restor-A-Finish

SDS Revision Date:

08/20/2014

4. First aid measures

4.1. Description of first aid measures

General

Move victim to fresh air. Keep victim warm and quiet.
Call 911 or emergency medical service if deemed necessary.
Give artificial respiration if victim is not breathing. Administer oxygen if breathing is difficult.
Remove and isolate contaminated clothing and shoes.
In case of contact with substance, immediately flush skin or eyes with running water.
Wash skin with soap and water.
In case of burns, immediately cool affected skin for as long as possible with cold water. Do not remove clothing if adhering to skin.
Ensure that medical personnel are aware of the material(s) involved and take precautions to protect themselves.

Inhalation

Remove to fresh air, keep patient warm and at rest. If breathing is irregular or stopped, give artificial respiration. If unconscious place in the recovery position and obtain immediate medical attention. Give nothing by mouth.

Eyes

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

Skin

Remove and isolate contaminated clothing and shoes. Clothing frozen to the skin should be thawed before being removed. In case of contact with liquefied gas, thaw frosted parts with lukewarm water.

Ingestion

If swallowed obtain immediate medical attention. Keep at rest. Do NOT induce vomiting.

4.2. Most important symptoms and effects, both acute and delayed

Overview

Exposure to solvent vapor concentrations from the component solvents in excess of the stated occupational exposure limits may result in adverse health effects such as mucous membrane and respiratory system irritation and adverse effects on the kidneys, liver and central nervous system. Symptoms include headache, nausea, dizziness, fatigue, muscular weakness, drowsiness and in extreme cases, loss of consciousness.

Repeated or prolonged contact with the preparation may cause removal of natural fat from the skin resulting in dryness, irritation and possible non-allergic contact dermatitis. Solvents may also be absorbed through the skin. Splashes of liquid in the eyes may cause irritation and soreness with possible reversible damage. See section 2 for further details.

Inhalation

Harmful if inhaled.

Eyes

Causes serious eye irritation.

Skin

Causes mild skin irritation. (Not adopted by US OSHA)

Safety Data Sheet

Restor-A-Finish

SDS Revision Date:

08/20/2014

5. Fire-fighting measures

5.1. Extinguishing media

Recommended extinguishing media; alcohol resistant foam, CO₂, powder, water spray.
Do not use; water jet.

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition: High temperatures and fires may produce such toxic substances as carbon monoxide and carbon dioxide.

Keep away from heat / sparks / open flames / hot surfaces - No smoking.

Use explosion-proof electrical / ventilating / light / equipment.

Avoid breathing dust / fume / gas / mist / vapors / spray.

5.3. Advice for fire-fighters

Wear positive pressure self-contained breathing apparatus (SCBA).

Structural firefighters' protective clothing will only provide limited protection.

HIGHLY FLAMMABLE: Will be easily ignited by heat, sparks or flames.

Vapors may form explosive mixtures with air.

Vapors may travel to source of ignition and flash back.

Most vapors are heavier than air. They will spread along ground and collect in low or confined areas (sewers, basements, tanks).

Vapor explosion hazard indoors, outdoors or in sewers. Runoff to sewer may create fire or explosion hazard.

Containers may explode when heated.

Many liquids are lighter than water.

Inhalation or contact with material may irritate or burn skin and eyes.

Fire may produce irritating, corrosive and/or toxic gases.

Vapors may cause dizziness or suffocation.

Runoff from fire control may cause pollution.

ERG Guide No. 127

6. Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Water spray may reduce vapor; but may not prevent ignition in closed spaces.

6.2. Environmental precautions

Do not allow spills to enter drains or watercourses.

Use good personal hygiene practices. Wash hands before eating, drinking, smoking or using toilet. Promptly remove soiled clothing and wash thoroughly before reuse.

6.3. Methods and material for containment and cleaning up

As an immediate precautionary measure, isolate spill or leak area for at least 50 meters (150 feet) in all directions.

Keep unauthorized personnel away.

Stay upwind. Keep out of low areas. Ventilate closed spaces before entering.

Safety Data Sheet

Restor-A-Finish

SDS Revision Date:

08/20/2014

7. Handling and storage

7.1. Precautions for safe handling

Store in accordance with the National Fire Protection Association's publication NFPA 30, Flammable and Combustible Liquids Code. 29 CFR 1910.106 applies to the handling, storage, and use of flammable and combustible liquids. See section 2 for further details. - [Prevention]:

7.2. Conditions for safe storage, including any incompatibilities

Handle containers carefully to prevent damage and spillage.

Incompatible materials: Strong oxidizing agents and acids.

See section 2 for further details. - [Storage]:

7.3. Specific end use(s)

No data available.

8. Exposure controls and personal protection

8.1. Control parameters

Exposure

CAS No.	Ingredient	Source	Value
0000067-63-0	Isopropyl Alcohol	OSHA	TWA 400 ppm (980 mg/m ³) STEL 500 ppm
		ACGIH	TWA: 200 ppm STEL: 400 ppm Revised 2003,
		NIOSH	TWA 400 ppm (980 mg/m ³) ST 500 ppm (1225 mg/m ³)
		Supplier	No Established Limit
0000067-64-1	Acetone	OSHA	TWA 1000 ppm (2400 mg/m ³) STEL 2400 mg/m ³
		ACGIH	TWA: 250 ppm STEL: 500 ppm Skin
		NIOSH	250 ppm (590 mg/m ³) TWA
		Supplier	No Established Limit
0000078-93-3	Butanone	OSHA	TWA 200 ppm (590 mg/m ³)
		ACGIH	TWA: 50 ppm STEL: 100 ppm
		NIOSH	TWA 200 ppm (590 mg/m ³) ST 300 ppm (885 mg/m ³)
		Supplier	No Established Limit
0001330-20-7	Xylene	OSHA	STEL 150 ppm
		ACGIH	TWA: 100 ppm STEL: 150 ppm
		NIOSH	No Established Limit
		Supplier	No Established Limit
0064742-47-8	Petroleum distillates, hydrotreated light	OSHA	No Established Limit
		ACGIH	No Established Limit
		NIOSH	No Established Limit
		Supplier	Recommended 300 ppm PEL
0064742-54-7	Distillates (petroleum), hydrotreated heavy paraffinic	OSHA	No Established Limit
		ACGIH	No Established Limit
		NIOSH	No Established Limit
		Supplier	No Established Limit

Contains mineral oil. The exposure limits for oil mist are 5 mg/m³ OSHA PEL and 10 mg/m³ ACGIH.

Safety Data Sheet

Restor-A-Finish

SDS Revision Date:

08/20/2014

This product contains no known or suspected carcinogens and is not believed to be carcinogenic.

8.2. Exposure controls

Respiratory	If workers are exposed to concentrations above the exposure limit they must use the appropriate, certified respirators.
Eyes	Safety glasses with side shields
Skin	Wear overalls to keep skin contact to a minimum. Impervious rubber gloves
Engineering Controls	Provide adequate ventilation. Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction. If these are not sufficient to maintain concentrations of particulates and any vapor below occupational exposure limits suitable respiratory protection must be worn.
Other Work Practices	Use good personal hygiene practices. Wash hands before eating, drinking, smoking or using toilet. Promptly remove soiled clothing and wash thoroughly before reuse.

See section 2 for further details. - [Prevention]:

9. Physical and chemical properties

Appearance	Clear to dark Liquid
Odor	Aromatic
Odor threshold	Not Available
pH	Not Established
Melting point / freezing point	Not Established
Initial boiling point and boiling range	> 93.33 C (> 200 F)
Flash Point	3.88 C (39 F)
Evaporation rate (Ether = 1)	Less than Bu Acetate
Flammability (solid, gas)	Not Applicable
Upper/lower flammability or explosive limits	Not Established
Vapor pressure (Pa)	51.2 mmHg @20C
Vapor Density	> 1
Specific Gravity	0.87
Solubility in Water	Insoluble
Partition coefficient n-octanol/water (Log Kow)	Not Measured
Auto-ignition temperature	Not Established
Decomposition temperature	Not Established
Viscosity (cSt)	Not Established
VOC %	Not Established
% Volatile	Not available

9.2. Other information

DMSO extract by IP346: Less than 3.0 wt % (mineral oil component only)

Safety Data Sheet

Restor-A-Finish

SDS Revision Date:

08/20/2014

10. Stability and reactivity

10.1. Reactivity

Hazardous Polymerization will not occur.

10.2. Chemical stability

Stable under normal circumstances.

10.3. Possibility of hazardous reactions

No data available.

10.4. Conditions to avoid

Excessive heat and open flame.

10.5. Incompatible materials

Strong oxidizing agents and acids.

10.6. Hazardous decomposition products

High temperatures and fires may produce such toxic substances as carbon monoxide and carbon dioxide.

11. Toxicological information

Acute toxicity

Exposure to solvent vapor concentrations from the component solvents in excess of the stated occupational exposure limits may result in adverse health effects such as mucous membrane and respiratory system irritation and adverse effects on the kidneys, liver and central nervous system. Symptoms include headache, nausea, dizziness, fatigue, muscular weakness, drowsiness and in extreme cases, loss of consciousness.

Repeated or prolonged contact with the preparation may cause removal of natural fat from the skin resulting in dryness, irritation and possible non-allergic contact dermatitis. Solvents may also be absorbed through the skin. Splashes of liquid in the eyes may cause irritation and soreness with possible reversible damage.

Ingredient	Oral LD50, mg/kg	Skin LD50, mg/kg	Inhalation Vapor LD50, mg/L/4hr	Inhalation Dust/Mist LD50, mg/L/4hr	Inhalation Gas LD50, ppm
Distillates (petroleum), hydrotreated heavy paraffinic - (64742-54-7)	5,000.00, Rat - Category: 5	No data available	No data available	2.18, Rat - Category: 4	No data available
Petroleum distillates, hydrotreated light - (64742-47-8)	5,000.00, Rat - Category: 5	>2,000.00, Rabbit - Category: 5	No data available	No data available	No data available
Isopropyl Alcohol - (67-63-0)	4,710.00, Rat - Category: 5	12,800.00, Rat - Category: NA	72.60, Rat - Category: NA	No data available	No data available
Acetone - (67-64-1)	2,000.00, Rat - Category: 4	2,000.00, Rabbit - Category: 4	76.00, Rat - Category: NA	No data available	No data available
Butanone - (78-93-3)	2,737.00, Rat - Category: 5	6,480.00, Rabbit - Category: NA	32.00, Mouse - Category: NA	No data available	No data available
Xylene - (1330-20-7)	4,299.00, Rat - Category: 5	1,548.00, Rabbit - Category: 4	No data available	20.00, Rat - Category: NA	5,000.00, Rat - Category: 4
Gilsonite - (12002-43-6)	No data available	No data available	No data available	No data available	No data available

Note: When no route specific LD50 data is available for an acute toxin, the converted acute toxicity point estimate was used in the calculation of the product's ATE (Acute Toxicity Estimate).

Safety Data Sheet

Restor-A-Finish

SDS Revision Date:

08/20/2014

Classification	Category	Hazard Description
Acute toxicity (oral)	---	Not Applicable
Acute toxicity (dermal)	---	Not Applicable
Acute toxicity (inhalation)	4	Harmful if inhaled.
Skin corrosion/irritation	3	Causes mild skin irritation. (Not adopted by US OSHA)
Serious eye damage/irritation	2	Causes serious eye irritation.
Respiratory sensitization	---	Not Applicable
Skin sensitization	---	Not Applicable
Germ cell mutagenicity	---	Not Applicable
Carcinogenicity	---	Not Applicable
Reproductive toxicity	---	Not Applicable
STOT-single exposure	---	Not Applicable
STOT-repeated exposure	---	Not Applicable
Aspiration hazard	---	Not Applicable

12. Ecological information

12.1. Toxicity

Aquatic Ecotoxicity

Ingredient	96 hr LC50 fish, mg/l	48 hr EC50 crustacea, mg/l	ErC50 algae, mg/l
Distillates (petroleum), hydrotreated heavy paraffinic - (64742-54-7)	5,000.00, Oncorhynchus mykiss	1,000.00, Daphnia magna	Not Available
Petroleum distillates, hydrotreated light - (64742-47-8)	Not Available	Not Available	Not Available
Isopropyl Alcohol - (67-63-0)	1,400.00, Lepomis macrochirus	100.00, Daphnia magna	100.00 (72 hr), Scenedesmus subspicatus
Acetone - (67-64-1)	100.00, Pimephales promelas	10.00, Daphnia magna	20.565 (72 hr), Ulva pertusa
Butanone - (78-93-3)	400.00, Cyprinodon variegatus	520.00, Daphnia magna	500.00 (96 hr), Skeletonema costatum
Xylene - (1330-20-7)	3.30, Oncorhynchus mykiss	8.50, Palaemonetes pugio	100.00 (72 hr), Chlorococcales
Gilsonite - (12002-43-6)	Not Available	Not Available	Not Available

12.2. Persistence and degradability

There is no data available on the preparation itself.

12.3. Bioaccumulative potential

Not Measured

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

This product contains no PBT/vPvB chemicals.

12.6. Other adverse effects

No data available.

Safety Data Sheet

Restor-A-Finish

SDS Revision Date:

08/20/2014

13. Disposal considerations

13.1. Waste treatment methods

Do not allow into drains or water courses. Wastes and emptied containers should be disposed of in accordance with regulations made under the Control of Pollution Act and the Environmental Protection Act. Using information provided in this data sheet advice should be obtained from the Waste Regulation Authority, whether the special waste regulations apply.

14. Transport information

	DOT	IMO / IMDG	ICAO/IATA
14.1. UN number	UN1263	UN1263	UN1263
14.2. UN proper ship. name	UN1263, Paint, 3, III	Paint	Paint
14.3. Transport hazard class(es)	DOT Hazard Class: 3 DOT Label: 3	IMDG: 3 Sub Class: Not Applicable	Air Class: 3
14.4. Packing group	III	III	III
14.5. Environmental hazards			

IMDG Marine Pollutant: No

14.6. Special precautions for user

No further information

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not Applicable

Safety Data Sheet

Restor-A-Finish

SDS Revision Date:

08/20/2014

15. Regulatory information

Regulatory Overview The regulatory data in Section 15 is not intended to be all-inclusive, only selected regulations are represented. All ingredients of this product are listed on the TSCA (Toxic Substance Control Act) Inventory or are not required to be listed on the TSCA Inventory.

WHMIS Classification B2 D2B

US EPA Tier II Hazards **Fire:** Yes

Sudden Release of Pressure: No

Reactive: No

Immediate (Acute): Yes

Delayed (Chronic): No

EPCRA 311/312 Chemicals and RQs (lbs):

Acetone (5,000.00)

Butanone (5,000.00)

Xylene (100.00)

EPCRA 302 Extremely Hazardous :

(No Product Ingredients Listed)

EPCRA 313 Toxic Chemicals:

Ethyl Benzene

Isopropyl Alcohol

Xylene

Proposition 65 - Carcinogens (>0.0%):

Ethyl Benzene

Proposition 65 - Developmental Toxins (>0.0%):

Toluene

Proposition 65 - Female Repro Toxins (>0.0%):

(No Product Ingredients Listed)

Proposition 65 - Male Repro Toxins (>0.0%):

(No Product Ingredients Listed)

N.J. RTK Substances (>1%):

Acetone

Butanone

Isopropyl Alcohol

Xylene

Penn RTK Substances (>1%):

Acetone

Butanone

Isopropyl Alcohol

Safety Data Sheet

Restor-A-Finish

SDS Revision Date:

08/20/2014

Xylene

16. Other information

The information and recommendations contained herein are based upon data believed to be correct. However, no guarantee or warranty of any kind, expressed or implied, is made with respect to the information contained herein. We accept no responsibility and disclaim all liability for any harmful effects which may be caused by exposure to our products. Customers/users of this product must comply with all applicable health and safety laws, regulations, and orders.

The full text of the phrases appearing in section 3 is:

H225 Highly flammable liquid and vapor.

H226 Flammable liquid and vapor.

H304 May be fatal if swallowed and enters airways.

H312 Harmful in contact with skin.

H315 Causes skin irritation.

H319 Causes serious eye irritation.

H332 Harmful if inhaled.

H336 May cause drowsiness and dizziness.

H350 May cause cancer.

This is the first version in the GHS SDS format. Listings of changes from previous versions in other formats are not applicable.

Information contained herein was obtained from sources considered technically accurate and reliable. While every effort has been made to ensure full disclosure of product hazards, in some cases data is not available and is so stated. Since conditions of actual product use are beyond control of the supplier, it is assumed that users of this material have been fully trained according to the requirements of all applicable legislation and regulatory instruments. No warranty, expressed or implied, is made and supplier will not be liable for any losses, injuries or consequential damages which may result from the use of or reliance on any information contained in this document.

End of Document